



Modular LCD multimeters. non expandable
DMG200
Three-phase + neutral
4

Product designation

Product type designation

Type

DIN rail module number

Auxiliary supply Us

Auxiliary rated supply voltage AC	VAC	100...240
-----------------------------------	-----	-----------

Auxiliary rated supply voltage DC	VDC	110...250
-----------------------------------	-----	-----------

Auxiliary operating voltage range	AC		
		min	VAC 85
		Max	VAC 264

DC		min	VDC 93.5
		Max	VDC 300

Operational frequency		min	Hz 45
		max	Hz 66

Power consumption		Max	VA 3.5
-------------------	--	-----	--------

Power dissipation Max	W	1.2
-----------------------	---	-----

Measuring voltage inputs

Rated voltage (Ue)	phase-phase	VAC	690
	phase-neutral	VAC	400

Operating voltage range	phase-phase	VAC	20...830
	phase-neutral	VAC	10...480

Voltage inputs operational frequency		min	Hz 45
		max	Hz 66

Voltage inputs measurement method	True RMS		
-----------------------------------	----------	--	--

Connection method	Single. two.		
	three-phase with or without neutral. balanced three-phase systems		

Current inputs


Rated current (Ie)	A	5
--------------------	---	---

Measurement range	0.01...6		
-------------------	----------	--	--

Measurement method	TRMS		
--------------------	------	--	--


Overload capacity	+20% Ie through external CT with 5A secondary		
-------------------	---	--	--

Overload peak		A	50A for 1s
Accuracy			
	VLN voltage		±0.5%
	VLL voltage		±0.5%
	Current		±0.5%
	Frequency		±0.05%
	Active power		±1%
	Active energy		Class 1 (IEC/EN 62053-21)
	Reactive energy		Class 2 (IEC/EN 62053-23)
Insulations			
Rated insulation voltage Ui IEC/EN		V	690
Rated impulse withstand voltage Uimp		kV	9.5
Operating frequency withstand voltage		kV	5.2
Functions			
Harmonic analysis			THD only
PLC logic			No
Type of communication port			No
Ethernet-RS485 gateway function			No
Mechanical features			
Housing type			Polyamide
Terminals type			Fixed
Conductor cross section			
	min	mm ²	0.2
	Max	mm ²	4
	min	AWG	24
	Max	AWG	12
Tightening torque (Max)			
		Nm	0.8
		lbin	7
Fixing			Din rail
Weight		g	294
Ambient conditions			
Temperature			
	Operating temperature		
		min	°C -20
		max	°C +60
	Storage temperature		
		min	°C -30
		max	°C +80
Relative humidity		%	<90
Maximum Pollution degree			2
Protection degree			IP30
Dimensions			




Wiring diagrams


Single-phase





Two-phase




Three-phase with or without neutral



Three-phase without neutral in ARON connection



Balanced 3-phase connection with or without neutral



CODE	AUX SUPPLY
DMG100-110-200-210-300	100...240VAC 110...250VDC
DMG6...	100...440VAC 110...250VDC
DMG7000-7500-8000-9000	100...240VAC 110...250VDC



Certifications and compliance

Compliance

CSA C22.2 n°14

IEC/EN 61000-6-2

IEC/EN 61000-6-4

IEC/EN 61010-1

UL508

Certificates

cULus

EAC

GOST

RCM

ETIM classification

ETIM 8.0

EC002301 -
Multifunction
measuring
instrument