



Modular LCD
multimeters.
expandable
DMG300
Three-phase +
neutral
4

Product designation

Product type designation

Type

DIN rail module number

Auxiliary supply Us

Auxiliary rated supply voltage AC	VAC	100...240
Auxiliary rated supply voltage DC	VDC	110...250
Auxiliary operating voltage range		
AC	min	VAC 85
	Max	VAC 264
DC	min	VDC 93.5
	Max	VDC 300

Operational frequency

min	Hz	45
max	Hz	66

Power consumption

Max	VA	3.2
-----	----	-----

Power dissipation Max

W	1.3
---	-----

Measuring voltage inputs

Rated voltage (Ue)

phase-phase	VAC	690
phase-neutral	VAC	400

Operating voltage range

phase-phase	VAC	20...830
phase-neutral	VAC	10...480

Voltage inputs operational frequency

min	Hz	45
max	Hz	66

Voltage inputs measurement method

True RMS

Connection method

Single. two.
three-phase with
or without neutral.
balanced three-
phase systems

Current inputs

Rated current (Ie)

A	1 / 5
---	-------




Measurement range

0.01...1.2 /
0.01...6









Measurement method

TRMS

Overload capacity				+20% Ie through external CT with 5A secondary
Overload peak		A		50A for 1s
Accuracy				
	VLN voltage			±0.2%
	VLL voltage			±0.2%
	Current			±0.2%
	Frequency			±0.05%
	Active power			±0.5%
	Active energy			Class 0.5s (IEC/EN 62053-22)
	Reactive energy			Class 2 (IEC/EN 62053-23)
Insulations				
Rated insulation voltage Ui IEC/EN		V		690
Rated impulse withstand voltage Uimp		kV		9.5
Operating frequency withstand voltage		kV		5.2
Functions				
Harmonic analysis				31st order
PLC logic				No
Type of communication port				No
Ethernet-RS485 gateway function				Yes
Mechanical features				
Housing type				Polyamide
Terminals type				Fixed
Conductor cross section				
	min	mm ²		0.2
	Max	mm ²		4
	min	AWG		24
	Max	AWG		12
Tightening torque (Max)				
		Nm		0.8
		lbin		7
Fixing				Din rail
Weight		g		320
Ambient conditions				
Temperature				
Operating temperature				
	min	°C		-20
	max	°C		+60
Storage temperature				
	min	°C		-30
	max	°C		+80
Relative humidity		%		<90
Maximum Pollution degree				2
Protection degree				IP30
Dimensions				



Wiring diagrams



Certifications and compliance

Compliance

IEC/EN/BS 61000-6-2

IEC/EN/BS 61000-6-4

IEC/EN/BS 61010-1

ETIM classification

ETIM 8.0

EC002301 -
Multifunction
measuring
instrument