



Contact characteristics

Contact configuration	2 C/O		
Rated insulation voltage U_i IEC/EN	V	250	
Rated impulse withstand voltage U_{imp}	kV	6	
IEC Conventional free air thermal current $I_{th} \leq 40^\circ\text{C}$	A	10	
Maximum instantaneous current	A	15	
Rated current (I_n)	A	10	
Max contrrollable power in	AC-1	W	2000
	AC-15	VA	150
Rated operating power AC-1	VA		2500
Rated operating power AC-15	230 VAC		360
	VA		360
Single-phase motor control	230VAC		0,37
	kW		0,37
Rated operating current DC-1	30V	A	8
	110V	A	0,4
	220V	A	0,2
	V / mA		5 / 100
Minimum switching load	m Ω		100
Contact impedance	m Ω		100
Contact material	Ag/SnO ₂		

Operating times

Closing	ms	<15
Opening	ms	<20 (AC) / < 10 (DC)

Operations

Mechanical life	cycles	30000000
Electrical life AC1	cycles	100000

Coil characteristics

Relay control voltage	V	12VAC
Average coil consumption AC at 20°C	VA	0,9
Average coil consumption DC at 20°C	W	0,53
Operating range		

Maximum cycle frequency	cycles/h	1200
-------------------------	----------	------

Mechanical features

Max socket terminal tightening torque	Nm	1
Socket screw tightening tool (cross / flat blade)	PH1 / 4.5mm	
Conductor section	AWG/Kcmil	
	min	20
	max	14

IEC

min	mm ²	0.5
max	mm ²	2.5

Operating position

normal	Any
--------	-----

Fixing

On 35mm DIN rail and with screw

Ambient conditions

Temperature

Operating temperature

min	°C	-40
max	°C	+70

Storage temperature

min	°C	-40
max	°C	+85

Other features

Indication

Yes


Mechanical contact position indicator

Yes

Mechanical test actuator

Yes

Wiring diagrams



Certifications and compliance

Compliance

IEC/EN/BS 61810-1

Certificates

cURus

TUV

ETIM classification

ETIM 8.0

EC001437 -
Switching relay