



Level control
relay for
emptying or filling
function. Multi
voltage. Modular
version
LVM25
Emptying or filling

Product designation

Product type designation

Function

Auxiliary supply

Supply voltage Type	Multi voltage	
Rated voltage U_s	24...240VAC/DC	
Operating voltage range	0.85...1.1 U_s	
Rated frequency	Hz	50/60
Power consumption Max	VA	3
Power dissipation Max	W	1.2

Output characteristics

Number of connectable electrodes	Nr.	3
Type of electrode	Electrode and electrode holders: SN1 / SCM / CGL / PS31 / PS3S or similar	
Electrode voltage	10 V _{pp}	
Sensitivity	k Ω	2.5...100 adjustable

Time delay

Tripping time	s	≤ 1
Resetting time	s	≤ 1

Relay outputs


Number of relays	Nr.	1
Relay state	Normally de-energised, energises at tripping	
Contact arrangement	1 changeover contact C/O-SPDT	
Rated operational voltage AC (IEC)	VAC	250
Maximum switching voltage	VAC	400
IEC Conventional free air thermal current I _{th}	A	8
UL/CSA and IEC/EN 60947-5-1 designation	B300	
Electrical life (with rated load)	cycles	10 ⁵
Mechanical life	cycles	30x10 ⁶

Indications


Indication				1 green LED for power on 1 red LED for relay state
Functions				
3 detecting electrodes (MIN, MAX and COM)				Yes
5 detecting electrodes (MIN1, MAX1, MIN2, MAX2 and COM)				No
Sensitivity adjustment 2.5...50k Ω				No
Sensitivity adjustment 2.5...100k Ω				Yes
Sensitivity adjustment 2.5...200k Ω				No
Adjustable sensitivity full-scale value 25-50-100-200 k Ω				No
Separate sensitivity adjustment for MAX probe (foam detection)				No
Emptying function				Yes
Filling function				Yes
Emptying function with MIN and/or MAX alarm				No
Filling function with MIN and/or MAX alarm				No
Emptying function with pump priority change				No
Filling function with pump priority change				No
Tank filling, well drawing and alarm				No
Filling-emptying adjustment selector				Yes
Programming selector for 5 different				No
Motor start-up priority change				No
Connections				
Terminals type				Screw
Tightening torque for terminals		max	Nm	0.8
		max	Ibin	7
Conductor cross section				
	AWG/Kcmil	min	AWG	24
		Max	AWG	12
	IEC	min	mm ²	0.2
		Max	mm ²	4
Insulations				
Rated insulation voltage U_i			V	240
Rated impulse withstand voltage U_{imp}			kV	4
Operating frequency withstand voltage			kV	2
Double insulation Supply / relay / electrode			VAC	≤ 250
Ambient conditions				
Temperature				
	Operating temperature	min	$^{\circ}\text{C}$	-20
		max	$^{\circ}\text{C}$	+60
	Storage temperature	min	$^{\circ}\text{C}$	-30
		max	$^{\circ}\text{C}$	+80
Housing				
Execution				Modular DIN rail mounting
N° of modules				1
Material				Self-extinguishing polyamide

Mounting	35mm DIN rail (IEC/EN 60715) or by screws using extractable clips	
IEC degree of protection	IP40 on front / IP20 on terminals	
Dimensions (W x H x D)	mm	17.5 x 104.7 x 64.9
Weight	g	95

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

- CSA C22.2 n° 14
- IEC/EN 60255-5
- IEC/EN 61000-6-2
- IEC/EN 61000-6-3
- UL508

Certificates

cULus

EAC

ETIM classification

ETIM 8.0

EC001447 - (Fill)
level monitoring
relay