

Product designation	Two pedal, with safety lever on both pedals - both with cover		
Product type designation	KRD002		
General characteristics			
Material	Housing	Aluminium-zinc alloy	
Contact characteristics			
Type of contact	2NO+2NC Snap action		
Thermal current I _{th}	A	10	
IEC/EN 60947-5-1 designation	A300 Q300		
Rated insulation voltage U _i	V	440	
Rated impulse withstand voltage U _{imp}	kV	4	
Short-circuit protection with fuse	Class/A	10 gG fuse	
IEC Conventional free air thermal current I _{th}	A	10	
Resistance per pole (average value)	mΩ	<10	
Mechanical features			
Tightening torque (Max)	Contact terminals	Nm lbin	1 0.74lbft
Cable connection	Self-releasing screw terminal		
Cable entry	1 x M20		
Operations			
Mechanical life	cycles	>10000000	
Ambient conditions			
Temperature	Operating temperature	min °C	-25
		max °C	+70
	Storage temperature	min °C	-40
		max °C	+70
Resistance & Protection			
IP degree	Terminals	IP20	
	Body housing	IP54	
Pollution degree	3		
Certifications and compliance			
Compliance	EN 60447.		
	IEC/EN 60204-1		
	IEC/EN 60947-1		
	IEC/EN 60947-5-1		
Certificates	EAC		
ETIM classification			
ETIM 8.0	EC001258 - Foot switch		