



Product type designation

KXCN

**General characteristics**

Material

Housing

Aluminium-zinc alloy

**Contact characteristics**

Type of contact

1NO+1NC Snap action

Thermal current I<sub>th</sub>

A 10

IEC/EN 60947-5-1 designation

A300 Q300

Rated insulation voltage U<sub>i</sub>

V 440

Rated impulse withstand voltage U<sub>imp</sub>

kV 4

Short-circuit protection with fuse

Class/A 10 gG/SC QUICK FUSE

IEC Conventional free air thermal current I<sub>th</sub>

A 10

Resistance per pole (average value)

mΩ <10

Conductivity

10mA 5V

**Mechanical features**

Operating head fixing

Locking bayonet insert

Tightening torque (Max)

Switch fixing

Nm 2.5  
lbin 22.1

Contact terminals

Nm 0.8  
lbin 7

Body lid screw fixing

Nm 0.8  
lbin 7

Conductor section

AWG/Kcmil

min 16  
max 14

IEC

min mm<sup>2</sup> 1or 2  
max mm<sup>2</sup> 2.5

Cable connection

Self-releasing screw terminal

Cable entry

M20 on the sides

**Operations**

Mechanical life

cycles >10000000

**Ambient conditions**

Temperature

Operating temperature

min °C -25


Storage temperature	max	°C	+70
	min	°C	-40
	max	°C	+70

**Resistance & Protection**

IP degree	Terminals	IP20
	Body housing	IP65
Pollution degree		3

**Wiring diagrams**

**Snap action**



**1NO + 1NC**

**Certifications and compliance**

Compliance	CSA C22.2 n° 14
	EN 50047
	IEC/EN 60204-1
	IEC/EN 60947-1
	IEC/EN 60947-5-1
	UL508

Certificates	cULus
	EAC

**ETIM classification**

ETIM 8.0	EC002498 - Accessories/spare parts for low-voltage switch technology
----------	--