



Product type designation

KXB

**General characteristics**

Material

Housing

Polymer  
thermoplastic

**Contact characteristics**

Type of contact

2NO Slow action

Thermal current I<sub>th</sub>

A 10

Short-circuit protection with fuse

Class/A 10 gG/SC  
QUICK FUSE

IEC Conventional free air thermal current I<sub>th</sub>

A 10

Resistance per pole (average value)

mΩ <10

Conductivity

10mA 5V

**Mechanical features**

Operating head fixing

Locking bayonet  
insert

Tightening torque (Max)

Switch fixing

Nm 2.5  
lbin 22.1

Contact terminals

Nm 0.8  
lbin 7

Body lid screw fixing

Nm 0.8  
lbin 7

Conductor section

AWG/Kcmil

min 16  
max 14

IEC

min mm<sup>2</sup> 1 or 2  
max mm<sup>2</sup> 2.5

Cable connection

Self-releasing  
screw terminal

Weight

g 21

**Operations**

Mechanical life

cycles >10000000

**Ambient conditions**

Temperature

Operating temperature

min °C -25  
max °C +70

Storage temperature

min °C -40  
max °C +70

**Resistance & Protection**

IP degree


Terminals	IP20
Body housing	IP65

Pollution degree

3

**Wiring diagrams**

**Slow action**



**2NO**

**Certifications and compliance**

Compliance

- CSA C22.2 n° 14
- EN 50047
- IEC/EN 60204-1
- IEC/EN 60947-1
- IEC/EN 60947-5-1
- UL508

Certificates

- cURus
- EAC

**ETIM classification**

ETIM 8.0

EC000196 -  
 Contactor relay