




Product designation	Miniature circuit breaker (MCB)			
Product type designation	P1 MB			
Number of poles	1P+N			
Number of DIN modules	1			
Compliance	IEC			
<b>Electrical features</b>				
Rated insulation voltage $U_i$ IEC/EN	V	440		
Rated impulse withstand voltage $U_{imp}$	kV	4		
Rated operational voltage AC (IEC)	VAC	230		
Rated frequency	Hz	50/60		
Rated current ( $I_n$ )	A	10		
Tripping curve		B		
Short circuit rating (IEC)	kA	6		
Electrical life	cycles	10000		
Power dissipation per pole max	W	1.25		
<b>Ambient conditions</b>				
Operating temperature	min	°C	-40	
	max	°C	+70	
Storage temperature	min	°C	-40	
	max	°C	+80	
Max altitude		m	2000	
<b>Mechanical features</b>				
Operating position	normal		Vertical plan	
			35mm DIN rail	
Fixing				
Tightening torque for terminals	min	Nm	1.1	
	max	Nm	1.2	
	min	Ibin	9.7	
	max	Ibin	10.6	
Terminals tool	Pz 2			
Conductor section	IEC	min	mm <sup>2</sup>	1
		max	mm <sup>2</sup>	16
	AWG/Kcmil	min		14
		max		6
Mechanical life		cycles	20000	
Weight		g	115	
Frontal IP degree	IP20			
Pollution degree	2			

Grid distance as per Annex H.1 of IEC/EN60898-1 standard

mm 60

**Dimensions**



**Wiring diagrams**

**Certifications and compliance**

**Compliance**

IEC/EN 60898-1

IEC/EN 60947-2

**Certifications**

EAC

TÜV-Rheinland