




Product designation	Miniature circuit breaker (MCB)		
Product type designation	P1 MB		
Number of poles	1P+N		
Number of DIN modules	1		
Compliance	IEC		
Electrical features			
Rated insulation voltage U_i IEC/EN	V	440	
Rated impulse withstand voltage U_{imp}	kV	4	
Rated operational voltage AC (IEC)	VAC	230	
Rated frequency	Hz	50/60	
Rated current (I_n)	A	32	
Tripping curve		B	
Short circuit rating (IEC)	kA	6	
Electrical life	cycles	10000	
Power dissipation per pole max	W	2.46	
Ambient conditions			
Operating temperature	min	°C	-40
	max	°C	+70
Storage temperature	min	°C	-40
	max	°C	+80
Max altitude		m	2000
Mechanical features			
Operating position	normal		Vertical plan
			35mm DIN rail
Fixing			
Tightening torque for terminals	min	Nm	1.1
	max	Nm	1.2
	min	lbin	9.7
	max	lbin	10.6
Terminals tool	Pz 2		
Conductor section	IEC	min	mm ² 1
		max	mm ² 16
	AWG/Kcmil	min	14
		max	6
Mechanical life		cycles	20000
Weight		g	115
Frontal IP degree	IP20		
Pollution degree	2		

Grid distance as per Annex H.1 of IEC/EN60898-1 standard

mm 60

Dimensions



Wiring diagrams

Certifications and compliance

Compliance

IEC/EN 60898-1

IEC/EN 60947-2

Certifications

EAC

TÜV-Rheinland