

Product designation			Miniature circuit breaker (MCB)		
Product type designation			P1 MB		
Number of poles			2P		
Number of DIN modules			2		
Compliance			IEC / UL1077		
Electrical features					
Rated insulation voltage Ui IEC/EN			V	440	
Rated impulse withstand voltage Uimp			kV	4	
Rated operational voltage AC (IEC)			VAC	230/400	
Rated operational voltage DC			VDC	125	
Rated frequency			Hz	50/60	
Rated current (In)			A	1.6	
Tripping curve			D		
Short circuit rating (IEC)			kA	10	
Limiting class			3		
Electrical life			cycles	10000	
Power dissipation per pole max			W	1.07	
Ambient conditions					
Operating temperature			min	°C	-40
			max	°C	+70
Storage temperature			min	°C	-40
			max	°C	+80
Max altitude			m	2000	
Mechanical features					
Operating position			normal		Vertical plan
					35mm DIN rail
Fixing					
Tightening torque for terminals			min	Nm	1.8
			max	Nm	2
			min	lbin	16
			max	lbin	17.7
Terminals tool			Pz 2		
Conductor section			IEC		
			min	mm²	1
			max	mm²	35
			AWG/Kcmil		
			min		14
			max	kcmil	6
Mechanical life			cycles	20000	
Weight			g	230	
Frontal IP degree			IP20		
Pollution degree			2		
Grid distance as per Annex H.1 of IEC/EN60898-1 standard			mm	60	
ETIM classification					
ETIM 8.0			EC000042 - Miniature circuit breaker (MCB)		