





| | | | | |
|---|---------------------------------|---------------|-----------------|-----|
| Product designation | Miniature circuit breaker (MCB) | | | |
| Product type designation | P2 MB | | | |
| Number of poles | 4P | | | |
| Number of DIN modules | 6 | | | |
| Compliance | IEC / UL1077 | | | |
| Electrical features | | | | |
| Rated insulation voltage U_i IEC/EN | V | 400 | | |
| Rated impulse withstand voltage U_{imp} | kV | 6 | | |
| Rated operational voltage AC (IEC) | VAC | 230/400 | | |
| Rated frequency | Hz | 50/60 | | |
| Rated current (I_n) | A | 80 | | |
| Tripping curve | C | | | |
| Short circuit rating (IEC) | kA | 10 | | |
| Electrical life | cycles | 10000 | | |
| Power dissipation per pole max | W | 11.58 | | |
| Ambient conditions | | | | |
| Operating temperature | min | °C | -40 | |
| | max | °C | +70 | |
| Storage temperature | min | °C | -40 | |
| | max | °C | +80 | |
| Max altitude | m | 2000 | | |
| Mechanical features | | | | |
| Operating position | normal | Vertical plan | | |
| Fixing | 35mm DIN rail | | | |
| Tightening torque for terminals | min | Nm | 3.2 | |
| | max | Nm | 3.5 | |
| | min | lbin | 28.3 | |
| | max | lbin | 31 | |
| Terminals tool | Pz 2 | | | |
| Conductor section | IEC | min | mm ² | 2.5 |
| | | max | mm ² | 50 |
| | AWG/Kcmil | min | 14 | |
| | | max | 1/0 | |
| | Mechanical life | cycles | 10000 | |
| | Weight | g | 680 | |
| Frontal IP degree | IP20 | | | |
| Pollution degree | 3 | | | |

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

CSA C22.2 n°235. UR "UL Recognized" per Canada e USA.

IEC/EN 60947-2

UL 1077

Certifications

cURus

EAC

TÜV-Rheinland

ETIM classification

ETIM 8.0

EC000042 -
Miniature circuit
breaker (MCB)