





Product designation	MODULAR CONTACTOR		
Product type designation	CN		
Operating voltage type	AC/DC		
Number of poles	4		
Number of DIN modules	2		
Electrical features			
IEC Conventional free air thermal current I _{th}	A	32	
Operational current AC1 and AC-7a ≤400V	A	32	
Operational current AC-3 and AC-7b ≤400V	A	8.5	
Rated insulation voltage U _i IEC/EN	V	440	
Rated impulse withstand voltage U _{imp}	kV	4	
Minimum switching capacity		≥17V ≥50mA	
Power dissipation per pole (average value) I _{th}	W	2.5	
Control circuit			
Auxiliary rated supply voltage U _s		220VAC/VDC	
Auxiliary contacts	NO	Nr.	4
Average coil consumption ≤20°C	in-rush	W	3
	holding	W	3
Operating voltage	pick-up	min	%U _s 85
		max	%U _s 110
	drop-out	min	%U _s 20
		max	%U _s 75
Average time	Closing NO	min	ms 15
		max	ms 45
	Opening NO	min	ms 20
		max	ms 70
Operations			
Mechanical life		cycles	3000000
Electrical life AC-3		cycles	500000
Electrical life AC1		cycles	150000
Ambient conditions			
Operating temperature	min	°C	-25
	max	°C	+70
Storage temperature			

	min	°C	-30
	max	°C	80
Max altitude		m	2000
Mechanical features			
Fixing			DIN rail 35mm
Tightening torque for coil terminal			
	max	Nm	0.6
	max	lbin	0.6
Tightening torque for terminals			
	max	Nm	1.2
	max	lbin	0.9
Conductor section			
	Coil terminal		
	min	mm ²	1
	max	mm ²	2.5
	Power terminal		
	min	mm ²	1
	max	mm ²	10
Terminals tool			PZ2
Weight		g	260
Resistance & Protection			
Frontal IP degree			IP20
Pollution degree			3

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

IEC/EN 60947-1

IEC/EN 60947-4-1

IEC/EN 60947-5-1

IEC/EN 61095

Certificates

EAC