





Product designation				MODULAR CONTACTOR
Product type designation				CN
Operating voltage type				AC/DC
Number of poles				2
Number of DIN modules				1
Electrical features				
IEC Conventional free air thermal current I _{th}	A			32
Operational current AC1 and AC-7a ≤400V	A			32
Operational current AC-3 and AC-7b ≤400V	A			9
Rated insulation voltage U _i IEC/EN	V			440
Rated impulse withstand voltage U _{imp}	kV			4
Minimum switching capacity			≥17V ≥50mA	
Power dissipation per pole (average value) I _{th}	W			2.5
Control circuit				
Auxiliary rated supply voltage U _s			220VAC/VDC	
Auxiliary contacts	NO	Nr.	2	
Average coil consumption ≤20°C	in-rush	W	2.5	
	holding	W	2.5	
Operating voltage	pick-up	min	%U _s	85
		max	%U _s	110
	drop-out	min	%U _s	20
		max	%U _s	75
Average time	Closing NO	min	ms	15
		max	ms	45
	Opening NO	min	ms	25
		max	ms	50
Operations				
Mechanical life			cycles	3000000
Electrical life AC-3			cycles	500000
Electrical life AC1			cycles	150000
Ambient conditions				
Operating temperature	min	°C	-25	
	max	°C	+70	
Storage temperature				

	min	°C	-30
	max	°C	80
Max altitude		m	2000
Mechanical features			
Fixing			DIN rail 35mm
Tightening torque for coil terminal	max	Nm	0.6
	max	Ibin	0.6
Tightening torque for terminals	max	Nm	1.2
	max	Ibin	0.9
Conductor section			
	Coil terminal		
	min	mm ²	1
	max	mm ²	2.5
	Power terminal		
	min	mm ²	1
	max	mm ²	10
Terminals tool			PZ2
Weight		g	135
Resistance & Protection			
Frontal IP degree			IP20
Pollution degree			3
Dimensions			



Wiring diagrams



Certifications and compliance

Compliance

IEC/EN 60947-1

IEC/EN 60947-4-1

IEC/EN 60947-5-1

IEC/EN 61095

Certificates

EAC

ETIM classification

ETIM 8.0

EC000066 -
Power contactor,
AC switching