




Product designation	AUXILIARY CONTACTS		
Product type designation	CN		
Number of DIN modules	0.5		
<b>Electrical features</b>			
IEC Conventional free air thermal current I <sub>th</sub>	A	6	
Rated insulation voltage U <sub>i</sub> IEC/EN	V	500	
Rated impulse withstand voltage U <sub>imp</sub>	kV	4	
Minimum switching capacity	≥12V ≥5mA		
<b>Control circuit</b>			
Auxiliary contacts			
	NO	Nr.	1
	NC	Nr.	1
<b>Operations</b>			
Mechanical life		cycles	3000000
<b>Ambient conditions</b>			
Operating temperature			
	min	°C	-5
	max	°C	55
Storage temperature			
	min	°C	-30
	max	°C	80
Max altitude		m	2000
<b>Mechanical features</b>			
Tightening torque for terminals			
	max	Nm	0.8
Terminals tool	PZ2		
Weight		g	44
<b>Resistance &amp; Protection</b>			
Pollution degree	3		
<b>Dimensions</b>			



### Wiring diagrams



### Certifications and compliance

#### Compliance

IEC/EN 60947-1  
 IEC/EN 60947-4-1  
 IEC/EN 60947-5-1  
 IEC/EN 61095

#### Certificates

EAC

### ETIM classification

ETIM 8.0

EC000041 -  
 Auxiliary contact  
 block