





Product designation	MODULAR CONTACTOR		
Product type designation	CN		
Operating voltage type	AC/DC		
Number of poles	4		
Number of DIN modules	2		
<b>Electrical features</b>			
IEC Conventional free air thermal current I <sub>th</sub>	A	25	
Operational current AC1 and AC-7a ≤400V	A	25	
Operational current AC-3 and AC-7b ≤400V	A	8.5	
Rated insulation voltage U <sub>i</sub> IEC/EN	V	440	
Rated impulse withstand voltage U <sub>imp</sub>	kV	4	
Minimum switching capacity		≥17V ≥50mA	
Power dissipation per pole (average value) I <sub>th</sub>	W	2	
<b>Control circuit</b>			
Auxiliary rated supply voltage U <sub>s</sub>		220VAC/VDC	
Auxiliary contacts			
	NO	Nr.	4
Average coil consumption ≤20°C			
	in-rush	W	3
	holding	W	3
Operating voltage			
pick-up			
	min	%U <sub>s</sub>	85
	max	%U <sub>s</sub>	110
drop-out			
	min	%U <sub>s</sub>	20
	max	%U <sub>s</sub>	75
<b>Operating times</b>			
Average time			
Closing NO			
	min	ms	15
	max	ms	45
Opening NO			
	min	ms	20
	max	ms	70
<b>Operations</b>			
Mechanical life		cycles	3000000
Electrical life AC-3		cycles	500000
Electrical life AC1		cycles	200000
<b>Ambient conditions</b>			
Operating temperature			
	min	°C	-25
	max	°C	+70
Storage temperature			

	min	°C	-30
	max	°C	80
Max altitude		m	2000
<b>Mechanical features</b>			
Fixing			DIN rail 35mm
Tightening torque for coil terminal	max	Nm	0.6
	max	lbin	0.6
Tightening torque for terminals	max	Nm	1.2
	max	lbin	0.9
Conductor section			
Coil terminal	min	mm <sup>2</sup>	1
	max	mm <sup>2</sup>	2.5
Power terminal	min	mm <sup>2</sup>	1
	max	mm <sup>2</sup>	10
Terminals tool			PZ2
Weight		g	260
<b>Resistance &amp; Protection</b>			
Frontal IP degree			IP20
Pollution degree			3

**Dimensions**



**Wiring diagrams**



**Certifications and compliance**

**Compliance**

IEC/EN 60947-1

IEC/EN 60947-4-1

IEC/EN 60947-5-1

IEC/EN 61095

Certificates

EAC

ETIM classification

ETIM 8.0

EC000066 -  
Power contactor,  
AC switching