



Product designation	MODULAR CONTACTOR		
Product type designation	CNM		
Operating voltage type	AC/DC		
Manual control	YES		
Number of poles	2		
Number of DIN modules	1		
Electrical features			
IEC Conventional free air thermal current I _{th}	A	20	
Operational current AC1 and AC-7a ≤400V	A	20	
Operational current AC-3 and AC-7b ≤400V	A	9	
Rated insulation voltage U _i IEC/EN	V	440	
Rated impulse withstand voltage U _{imp}	kV	4	
Minimum switching capacity		≥17V ≥50mA	
Power dissipation per pole (average value) I _{th}	W	1.7	
Control circuit			
Auxiliary rated supply voltage U _s		12V AC/DC	
Auxiliary contacts	NO	Nr.	1
Average coil consumption ≤20°C	in-rush	W	2.5
	holding	W	2.5
Operating voltage	pick-up	min	%U _s 85
		max	%U _s 110
	drop-out	min	%U _s 20
		max	%U _s 75
Operating times			
Average time	Closing NO	min	ms 15
		max	ms 45
	Opening NO	min	ms 25
		max	ms 50
Operations			
Mechanical life		cycles	3000000
Electrical life AC-3		cycles	300000
Electrical life AC1		cycles	200000
Ambient conditions			
Operating temperature	min	°C	-25
	max	°C	+70

Storage temperature

min	°C	-30
max	°C	80

Max altitude

m	2000
---	------

Mechanical features

Fixing

DIN rail 35mm

Tightening torque for coil terminal

max	Nm	0.6
max	lbin	0.6

Tightening torque for terminals

max	Nm	1.2
max	lbin	0.9

Conductor section

Coil terminal

min	mm ²	1
max	mm ²	2.5

Power terminal

min	mm ²	1
max	mm ²	10

Terminals tool

PZ2

Weight

g 135

Resistance & Protection

Frontal IP degree

IP20

Pollution degree

3

ETIM classification

ETIM 8.0

EC001653 -
Installation
contactor for
distribution board