





Product designation	Voltage monitoring relays		
Product type designation	PMV55		
<b>General characteristics</b>			
Description	Minimum and maximum AC voltage relay		
Type of system	Single-phase		
<b>Power supply</b>			
Auxiliary supply voltage $U_s$	Self powered		
Operating voltage range	0.7...1.2 $U_e$		
Rated frequency	Hz	50/60 $\pm 5\%$	
Power consumption Max	VA	17	
Power dissipation Max	W	1.5	
<b>Control circuit</b>			
Rated voltage to control ( $U_e$ )	min	VAC	380
	Max	VAC	440
Voltage set-point ( $\%U_e$ )	min	%	80...95
	Max	%	105...115
Tripping delay		s	0.1...20
Resetting time		s	0.1...20 (0.5 at power up)
Resetting hysteresis		%	3
Instantaneous tripping for $U_e$	Voltage $< 70\% U_e$		
Type of reset	Automatic		
Repeat accuracy		%	$\pm 0.1$
<b>Relay outputs</b>			
Number of relays		Nr.	1
Relay state	Normally energised De-energises at tripping		
Contact arrangement	1 changeover SPDT		
Rated operational voltage AC (IEC)	VAC	250	
Maximum switching voltage	VAC	400	
IEC Conventional free air thermal current $I_{th}$	A	8	
UL/CSA and IEC/EN 60947-5-1 designation	B300		
Electrical life (with rated load)	cycles	100000	
Mechanical life	cycles	30000000	
<b>Functions</b>			
Modular version	2U		
Minimum AC voltage	Yes		
Maximum AC voltage	Yes		

Minimum frequency				No
Maximum frequency				No
<b>Indications</b>				
Indication				1 green LED for power on and tripping and 2 red LEDs for tripping
<b>Connections</b>				
Terminals type				Screw
Tightening torque for terminals		max	Nm	0.8
		max	lbin	7
Conductor cross section				
	AWG/Kcmil	min	AWG	24
		Max	AWG	12
	IEC	min	mm <sup>2</sup>	0.2
		Max	mm <sup>2</sup>	4
<b>Insulations</b>				
Rated insulation voltage Ui			V	440
Rated impulse withstand voltage Uimp			kV	6
Operating frequency withstand voltage			kV	4
<b>Ambient conditions</b>				
Temperature				
	Operating temperature	min	°C	-20
		max	°C	+60
	Storage temperature	min	°C	-30
		max	°C	+80
<b>Housing</b>				
Execution (n° of modules)				2
Material				Self-extinguishing polyamide
Mounting				35mm DIN rail (IEC/EN 60715)
IEC degree of protection				IP40 on front; IP20 at terminals
Dimensions (W x H x D)			mm	35.8 x 104.7 x 64.9
Weight			g	125
<b>Dimensions</b>				



**Wiring diagrams**



**Certifications and compliance**

**Compliance**

- CSA C22.2 n° 14
- IEC/EN 60255-5
- IEC/EN 61000-6-2
- IEC/EN 61000-6-3
- UL 508

**Certificates**

- cULus
- EAC

**ETIM classification**

ETIM 8.0

EC001438 -  
Voltage  
monitoring relay