






Product designation	Motor protection circuit breaker SM1RM			
Product type designation	SM1RM			
<b>Electrical features</b>				
Magnetic protection	yes			
Thermal protection	no			
Rated insulation voltage $U_i$ IEC/EN	V	690		
Rated impulse withstand voltage $U_{imp}$	kV	6		
Rated frequency	Hz	50/60		
Rated current ( $I_n$ )	A	32		
Magnetic tripping	13 x $I_n$			
Power dissipation per pole	min	W	2.49	
	max	W	4.42	
Operational short-circuit current breaking capacity ( $I_{cs}$ ) at AC	230V	kA	100	
	400V	kA	25	
	440V	kA	5	
	500V	kA	5	
	690V	kA	2	
	690V	kA	2	
Maximum short-circuit current breaking capacity ( $I_{cu}$ ) at AC	230V	kA	100	
	400V	kA	50	
	440V	kA	10	
	500V	kA	10	
	690V	kA	4	
	690V	kA	4	
IEC Utilization category	A			
<b>Operations</b>				
Mechanical life	cycles	100000		
Electrical life	cycles	100000		
<b>Mechanical features</b>				
Tightening torque for terminals	min	Nm	2.5	
	max	Nm	3	
	min	lbin	22	
	max	lbin	26.5	
Conductor section	AWG/Kcmil	min	16	
		max	8	
	Flexible w/o lug conductor section	min	mm <sup>2</sup>	1
		max	mm <sup>2</sup>	10
	Flexible c/w lug conductor section	min	mm <sup>2</sup>	1
		max	mm <sup>2</sup>	10

		max	mm <sup>2</sup>	10
Flexible with insulated spade lug conductor section		min	mm <sup>2</sup>	1
		max	mm <sup>2</sup>	10
Screwdriver				PH2
Cable stripping length	main circuit	mm		12
<b>Ambient conditions</b>				
Temperature				
Operating temperature				
		min	°C	-20
		max	°C	+60
Storage temperature				
		min	°C	-50
		max	°C	+80
Compensation temperature				
		min	°C	-20
		max	°C	+50
Max altitude			m	3000
Operating position	allowable			Any
Fixing				Screw / DIN rail 35mm
Weight			g	390
<b>UL technical data</b>				
Motor Disconnect				
	at 480V	kA		30
	at 600V	kA		30
	protection			200A class J
Group Motor Installation				
	at 480V	kA		30
	at 600V	kA		30
	protection			200A class J
Tap Conductor Protection				
	at 480Y/277V	kA		10

**Dimensions**



**Wiring diagrams**



**Certifications and compliance**

Certifications

CSA C22.2 n° 60947-4-1

IEC/EN 60947-1

IEC/EN 60947-2

IEC/EN 60947-4-1

UL60947-4-1

Compliance

cULus

EAC

ETIM classification

ETIM 8.0

EC000074 -  
Motor protection  
circuit-breaker