



Product designation	Undervoltage trip releases
Product type designation	SM1X
Description	Undervoltage trip releases
Accessories for	SM1P..., SM1R...

**Auxiliary contact characteristics**

Rated insulation voltage $U_i$ IEC/EN	V	690
Rated impulse withstand voltage $U_{imp}$	kV	4

**Operational characteristics**

Rated supply voltage AC	VAC	110
Rated frequency	Hz	50
In-rush consumption	VA	12
Holding consumption	VA	3.5
Release voltage	Us	35...70
Operating voltage	US	85...110

**Mechanical features**

Tightening torque for terminals	min	Nm	1
	max	Nm	1
	min	Ibin	9
	max	Ibin	9

Conductor section	AWG/Kcmil	min	18	
		max	14	
Flexible w/o lug conductor section		min	mm <sup>2</sup>	0.75
		max	mm <sup>2</sup>	2.5
Flexible c/w lug conductor section		min	mm <sup>2</sup>	0.75
		max	mm <sup>2</sup>	2.5

Operating position	normal	Vertical
	allowable	Any

Terminals	type	Screw	
	screw	M3.5	
	width	mm	7.2
	tool	Ph2	

Weight	g	130
--------	---	-----

**Operations**

Mechanical life	cycles	100000
-----------------	--------	--------

**Ambient conditions**

Temperature		
-------------	--	--

Operating temperature

min	°C	-20
max	°C	+60

Storage temperature

min	°C	-50
max	°C	+80


Max altitude

m 3000


IEC degree of protection

IP20

**Dimensions**



**Wiring diagrams**



**Certifications and compliance**

Compliance

CSA C22.2 n° 14

IEC/EN 60947-1

IEC/EN 60947-5-1

---

UL508

---

Certificates

cULus  
EAC

---

ETIM classification