



Product designation	Undervoltage trip releases with early-make contacts
Product type designation	SM1X
Description	Undervoltage trip releases
Accessories for	SM1R...

Auxiliary contact characteristics

Type of contact	2NO
Rated insulation voltage U_i IEC/EN	V 690
Rated impulse withstand voltage U_{imp}	kV 4
UL/CSA and IEC/EN 60947-5-1 designation	C600 - Q600
Min. conductivity	5V 10mA

Operating current AC15

24V	A	2.5
48V	A	2.5
60V	A	2.5
110V	A	1.5
230V	A	1.5
400V	A	0.95
500V	A	0.35
690V	A	0.3

Operating current DC13

24V	A	2.5
48V	A	2.5
60V	A	2.5
110V	A	0.55
125V	A	0.55
220V	A	0.27
600V	A	0.1

Operational characteristics

Rated supply voltage AC	VAC	110
Rated frequency	Hz	50
In-rush consumption	VA	12
Holding consumption	VA	3.5
Release voltage	Us	35...70
Operating voltage	US	85...110

Mechanical features



Tightening torque for terminals

min	Nm	1
max	Nm	1
min	lbin	9
max	lbin	9


Conductor section

AWG/Kcmil

	min		18
	max		14
Flexible w/o lug conductor section	min	mm ²	0.75
	max	mm ²	2.5
Flexible c/w lug conductor section	min	mm ²	0.75
	max	mm ²	2.5
Operating position	normal allowable		Vertical Any
Terminals	type screw width tool	mm	Screw M3.5 7.2 Ph2
Weight		g	130
Operations			
Mechanical life		cycles	100000
Ambient conditions			
Temperature	Operating temperature	min °C	-20
		max °C	+60
	Storage temperature	min °C	-50
		max °C	+80
Max altitude		m	3000
IEC degree of protection			IP20
Dimensions			



Wiring diagrams



Certifications and compliance

Compliance

CSA C22.2 n° 14

IEC/EN 60947-1

IEC/EN 60947-5-1

UL508

Certificates

cULus

EAC

ETIM classification