





Product designation	11RFNA9		
Product type designation	Motor protection relay		
General characteristics			
Number of poles	Nr.	3	
Overvoltage category	III		
Pollution degree	3		
Frontal IP degree	IP20		
Type of release	Thermal		
Protection fuse			
	gG (IEC)	A	32
	aM (IEC)	A	10
	RK5 (UL)	A	30
Phase failure detection	yes		
Reset mode	Automatic		
Power circuit characteristics			
Rated insulation voltage U_i IEC/EN	V	690	
Rated impulse withstand voltage U_{imp}	kV	8	
Rated operational voltage	V	690	
Operational frequency			
	min	Hz	0
	max	Hz	400
Operational current I_e			
	Operational current min	A	6
	Operational current max	A	10
Tripping class	10A		
Test Button	Yes		
Trip indicator	yes		
Terminals			
	type	screw and washer	
	screw	M4	
	width	mm	9.8
	tool	Phillips 2	
Tightening torque for terminals			
	min	Nm	2.3
	max	Nm	2.3
	min	lbin	1.7
	max	lbin	1.7
Conductor section			
	AWG/kcmil max	10	
Auxiliary circuit characteristics			
Auxiliary contacts			
	NO	Nr.	1
	NC	Nr.	1

Auxiliary Rated insulation voltage U_i IEC/EN	V	690
Auxiliary Rated impulse withstand voltage U_{imp}	kV	6
Auxiliary Rated operational voltage	V	690
Operating current AC15	24V	A 1.5
	120V	A 1.5
	240V	A 0.75
IEC Conventional free air thermal current I_{th}	A	10
Terminals	Auxiliary circuit type	screw and washer
	Auxiliary circuit screw	M3,5
	Auxiliary circuit width	mm 8
	Auxiliary circuit tool	Phillips 1
Conductor section	Auxiliary circuit Flexible w/o lug max	mm ² 2.5
	Auxiliary circuit Flexible c/w lug max	mm ² 2.5
Tightening torque for terminals	Auxiliary circuit min	Nm 1
	Auxiliary circuit max	Nm 1
	Auxiliary circuit min	Ibin 0.74
	Auxiliary circuit max	Ibin 0.74
UL/CSA and IEC/EN 60947-5-1 designation	C300-R300	
Ambient conditions		
Operating temperature	min	°C -20
	max	°C 55
Storage temperature	min	°C -55
	max	°C 70
Compensation temperature	min	°C -15
	max	°C 55
Max altitude	m	3000
Mechanical features		
Operating position	normal allowable	Vertical plan ±30°
	Fixing	Direct mounting on BG06... BG09... BG12...
Weight	g	123
UL technical data		
Full-load current (FLA) for three-phase AC motor	at 480V	A 10
	at 600V	A 10
Dimensions		



Wiring diagrams



Certifications and compliance

Compliance

CSA C22.2 n° 14
IEC/EN 60947-1
IEC/EN 60947-4-1
UL508

Certifications

CCC
CSA
cULus
EAC

ETIM classification

ETIM 8.0

EC000106 -
Thermal overload
relay