



Product designation				RF38
Product type designation				Motor protection relay
General characteristics				
Number of poles	Nr.			3
Overvoltage category				III
Pollution degree				3
Frontal IP degree				IP20
Terminals IP degree				-
Type of release				Thermal
Protection fuse				
		gG (IEC)	A	32
		aM (IEC)	A	16
		RK5 (UL)	A	50
Phase failure detection				yes
Reset mode				Manual or automatic
Power circuit characteristics				
Rated insulation voltage U_i IEC/EN	V			690
Rated impulse withstand voltage U_{imp}	kV			6
Rated operational voltage	V			690
Operational frequency		min	Hz	0
		max	Hz	400
Operational current I_e				
		Operational current min	A	9
		Operational current max	A	14
Tripping class				10A
Test Button				Yes
Trip indicator				yes
Terminals				
		type	screw and washer	
		screw width	mm	M4
		width	mm	12.6
		tool	Phillips 2	
Tightening torque for terminals				
		min	Nm	2
		max	Nm	2.5
		min	lbin	1.5
		max	lbin	1.8
Conductor section				
		Flexible w/o lug max	mm ²	10
		Flexible c/w lug max	mm ²	6
		AWG/kcmil max		8

Auxiliary circuit characteristics

Auxiliary contacts

	NO	Nr.	1
	NC	Nr.	1

Auxiliary Rated insulation voltage U_i IEC/EN	V	690
---	---	-----

Auxiliary Rated impulse withstand voltage U_{imp}	kV	6
---	----	---

Auxiliary Rated operational voltage	V	690
-------------------------------------	---	-----

Operating current AC15	24V	A	3
	120V	A	3
	240V	A	1.5
	380V	A	0.95
	480V	A	0.75
	500V	A	0.72
	600V	A	0.6

Operating current DC13	125V	A	0.11
	600V	A	0.22

IEC Conventional free air thermal current I_{th}	A	10
--	---	----

Terminals

Auxiliary circuit type		screw and washer
Auxiliary circuit screw		M3.5
Auxiliary circuit width	mm	8
Auxiliary circuit tool		Phillips 2

Conductor section	Auxiliary circuit Flexible w/o lug max	mm ²	2.5
	Auxiliary circuit Flexible c/w lug max	mm ²	2.5

Tightening torque for terminals	Auxiliary circuit min	Nm	0.8
	Auxiliary circuit max	Nm	1
	Auxiliary circuit min	Ibin	0.6
	Auxiliary circuit max	Ibin	0.74

UL/CSA and IEC/EN 60947-5-1 designation	B600-R300
---	-----------

Ambient conditions

Operating temperature	min	°C	-25
	max	°C	60

Storage temperature	min	°C	-50
	max	°C	70

Compensation temperature	min	°C	-20
	max	°C	60

Max altitude	m	3000
--------------	---	------

Mechanical features

Operating position	normal allowable	Vertical plan ±30°
--------------------	------------------	--------------------

Fixing		Direct mounting on BF09... BF38...
--------	--	------------------------------------

Weight	g	160
--------	---	-----


UL technical data

Full-load current (FLA) for three-phase AC motor


at 480V	A	14
at 600V	A	14

Dimensions


BF00 A... BF09 A... - BF12 A... - BF18 A... - BF25 A... three poles with **RF...38** thermal overload relay



BF26 00A... - BF32 00A... - BF38 00A... three poles with **RF...38** thermal overload relay



Wiring diagrams



Certifications and compliance

Compliance

CSA C22.2 n° 14

IEC/EN 60947-1

IEC/EN 60947-4-1

UL508

Certifications

CCC

cULus

EAC

ETIM classification

ETIM 8.0

EC000106 -
Thermal overload
relay