



Product designation
Product type designation

Description

Accessories for

Motor operator
P5X192D024UL
Motor operator
for remote
operation for UL
certified MCCBs..
Accessories for
UL-compliant
MCCBs

Operational characteristics

Rated operational voltage	V	24VDC
Rated current (In)	A	≤2.5A
Mechanical operation	cycles/h	60
Average closing time	ms	500
Average opening time	ms	350
Power consumption	W	35


Mechanical features


Weight	g	3500
--------	---	------

Operations

Mechanical life	cycles	20000
-----------------	--------	-------

Dimensions





Note: Connect an NC contact of an alarm switch contact block in series with S4 to prevent remote closing of the MCCB after tripping due to overcurrent or short circuit.

Wiring diagrams

Certifications and compliance

Certificates

cULus

ETIM classification

EC000066 - Power contactor, AC switching