



Product designation				Monoblock actuators
Product type designation				LMPS1
General characteristics				
Colour				Black
Type of positions				Monoblock selector switch
IEC degree of protection				IP66 on front, IP20 on terminals
Electrical characteristics				
Rated insulation voltage U_i IEC/EN	V			300
IEC Conventional free air thermal current I_{th}	A			5
UL/CSA and IEC/EN 60947-5-1 designation				B300 R300
Operating current AC12	12V	A	5	
	30V	A	5	
	125V	A	4	
	250V	A	2	
	Operating current AC15	12V	A	5
30V		A	5	
125V		A	3	
250V		A	1.5	
Operating current DC12		12V	A	1
	30V	A	1	
	125V	A	0.32	
	250V	A	0.16	
	Operating current DC13	12V	A	1
30V		A	1	
125V		A	0.22	
250V		A	0.11	
Operations				
Electrical life			cycles	250000
Mechanical features				
Mechanical life			cycles	250000
Conductor section	AWG/kcmil conductor section			
		min	26	
		max	16	
IEC		min	mm ²	0.2
		max	mm ²	1.5
Ambient conditions				
Temperature				


Operating temperature

min	°C	-25
max	°C	+70

Storage temperature

min	°C	-40
max	°C	+85

Dimensions



Wiring diagrams

