



Monoblock buzzer  
- Continuous or pulse tone  
LPCZS

Product designation

Product type designation

**General characteristics**

Type of positions	Buzzer
Material	Polyamide
IEC degree of protection	IP66, IP67; IP96K on front and IP20 on rear

**Electrical characteristics**

Rated impulse withstand voltage Uimp	kV	4
Rated frequency	Hz	50-60
Supply voltage (AC)	V	9...15
Supply voltage (DC)	V	9...15

**Mechanical features**

Tightening torque for terminals max	Nm	0.5
Screwdriver	Flat-head: 0.6x3.5mm/0.02x0.	
Conductor section		

AWG/kcmil conductor section

min	24
max	14

IEC

min	mm <sup>2</sup>	0.5
max	mm <sup>2</sup>	2.5

Weight	g	20
--------	---	----

**UL technical data**

UL degree of protection	1, 2, 3R, 4, 4X, 12, 12K on front
-------------------------	--------------------------------------

**Ambient conditions**

Temperature


Operating temperature

min	°C	-25
max	°C	+70


Storage temperature

min	°C	-40
max	°C	+85

**Dimensions**



Wiring diagrams



Certifications and compliance

Compliance

CSA C22.2 n° 14  
 IEC/EN/BS 60947-1  
 IEC/EN/BS 60947-5-1  
 UL508

Certificates

CCC  
 cULus  
 EAC

ETIM classification

ETIM 8.0

EC000130 -  
 Signal horn