



Monoblock buzzer
- Continuous or
pulse tone
LPCZS

Product designation

Product type designation

General characteristics

Type of positions

Buzzer

Material

Polyamide

IEC degree of protection

IP40 on front and
IP20 on rear

Electrical characteristics

Rated impulse withstand voltage U_{imp}

kV 4

Rated frequency

Hz 50-60

Supply voltage (AC)

V 185...265

Supply voltage (DC)

V 185...265

Mechanical features

Tightening torque for terminals max

Nm 0.5

Screwdriver

Flat-head:
0.6x3.5mm/0.02x0.

Conductor section

AWG/kcmil conductor section

min	24
max	14

IEC

min	mm ²	0.5
max	mm ²	2.5

Weight

g 20

UL technical data

UL degree of protection

1, 2, 3R, 4, 4X,
12, 12K on front

Ambient conditions

Temperature


Operating temperature

min	°C	-25
max	°C	+70


Storage temperature

min	°C	-40
max	°C	+85

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

CSA C22.2 n° 14

IEC/EN/BS 60947-1

IEC/EN/BS 60947-5-1

UL508

Certificates

CCC

cULus

EAC

ETIM classification

ETIM 8.0

EC000130 -
Signal horn