



Illuminated  
selector switch  
actuator - 2  
position  
LPFSL12

Product designation

Product type designation

General characteristics

|                          |                          |
|--------------------------|--------------------------|
| Colour                   | Red                      |
| Type of positions        | 0 - 1                    |
| Material                 | Aluminium and zinc alloy |
| IEC degree of protection | IP66, IP67 and IP69K     |

Mechanical features

|                  |                          |         |
|------------------|--------------------------|---------|
| Mechanical life  | cycles                   | 1000000 |
| Fixing           | Without mounting adapter |         |
| Mounting adapter | LPXAU120M                |         |

UL technical data

|                         |                              |
|-------------------------|------------------------------|
| UL degree of protection | Type1, 2, 3R, 4, 4X, 12, 12K |
|-------------------------|------------------------------|

Ambient conditions

Temperature


Operating temperature

|     |    |     |
|-----|----|-----|
| min | °C | -25 |
| max | °C | +70 |

Storage temperature

|     |    |     |
|-----|----|-----|
| min | °C | -40 |
| max | °C | +85 |

Dimensions



Lever

Certifications and compliance

Compliance

|                     |
|---------------------|
| CSA C22.2 n° 14     |
| IEC/EN/BS 60947-1   |
| IEC/EN/BS 60947-5-1 |
| UL508               |

Certificates

cULus

ETIM classification

ETIM 8.0

EC002611 -  
Control switch