



| | |
|--------------------------|---|
| Product designation | Selector switch actuator key - 2 position |
| Product type designation | LPSS32 |

General characteristics

| | |
|--------------------------|----------------------------------|
| Colour | Black |
| Type of positions | 0 - 1, key extraction in 0 and 1 |
| Material | Aluminium and zinc alloy |
| IEC degree of protection | IP66, IP67 and IP69K |

Mechanical features

| | | |
|------------------|--------------------------|---------|
| Mechanical life | cycles | 1000000 |
| Fixing | Without mounting adapter | |
| Mounting adapter | LPXAU120M | |


UL technical data

| | |
|-------------------------|------------------------------|
| UL degree of protection | Type1, 2, 3R, 4, 4X, 12, 12K |
|-------------------------|------------------------------|

Ambient conditions

| | | | | |
|-------------|-----------------------|-----|----|-----|
| Temperature | Operating temperature | min | °C | -25 |
| | | max | °C | +70 |
| | Storage temperature | min | °C | -40 |
| | | max | °C | +85 |

Dimensions



Certifications and compliance

| | |
|------------|---------------------|
| Compliance | CSA C22.2 n° 14 |
| | IEC/EN/BS 60947-1 |
| | IEC/EN/BS 60947-5-1 |
| | UL508 |

| | |
|--------------|-------|
| Certificates | cULus |
|--------------|-------|

ETIM classification

ETIM 8.0

EC002611 -
Control switch