


Product designation				Rotary cam switches		
Product type designation				7GN125		
<b>General characteristics</b>						
Switching diagram				52 - Changeover switch 2 poles		
N° of elements				2		
Mounting form				O - Rear mounting with black handle		
<b>Contact characteristics</b>						
Rated insulation voltage $U_i$	IEC/EN	V	690			
	UL/CSA	V	600			
Rated impulse withstand voltage $U_{imp}$			kV	6		
Conventional free air thermal current $I_{th}$	IEC/EN	A	125			
	UL/CSA	A	130			
Rated operational voltage			V	690		
Rated operational impulse voltage			kV	6		
Maximum fuse size for short-circuit protection $I_n$ (gG)	10kA	A	125			
	15kA	A	100			
	25kA	A	100			
	50kA	A	100			
	63kA	A	100			
Rated short time current $I_{cw}$	1s	kA	2100			
				10/5 mA/V		
Conductivity				10/5 mA/V		
Operational current $I_e$ IEC/EN	AC1/AC21A			A	125	
	AC15			110V	A	40
Rated operational power in AC				220/230V	A	28
				380/400V	A	15
				660/690V	A	5
	Three-phase AC-3			220/230V	kW	18.5
				380/440V	kW	37
				500/690V	kW	33
	Single-phase AC-3			110V	kW	5
				220/230V	kW	11
				380/440V	kW	15
	Three-phase AC23A			220/230V	kW	30
				380/440V	kW	45
				500/690V	kW	37
Single-phase AC23A			110V	kW	5	
			220/230V	kW	11	

		380/440V	kW	15
Rated operational current in DC				
DC21A		48V	A	125
		60V	A	80
		110V	A	10
		220V	A	1.2
DC23A (poles in series)		24V	A	125 (1)
		48V	A	125 (2)
		60V	A	125 (3)
		110V	A	50 (3)
		220V	A	20 (4)
DC13		24V	A	125
		48V	A	100
		60V	A	50
		110V	A	4
Power dissipation			W	6.3
<b>Mechanical features</b>				
Terminals screw				M2X5
Tightening torque for terminals max			Nm	2
Conductor size				
AWG - Rigid cable		min	AWG	14
		Max	AWG	1/0
AWG - Flexible cable		min	AWG	14
		Max	AWG	1/0
Conductor size (IEC) - Flexible cable		min	mm <sup>2</sup>	2.5
		Max	mm <sup>2</sup>	50
Conductor size (IEC) - Rigid cable		min	mm <sup>2</sup>	2.5
		Max	mm <sup>2</sup>	50
Mechanical life			cycles	1X10 <sup>6</sup>
<b>UL technical data</b>				
Motor power for direct-on-line control				
for three-phase motor		120V	HP	15
		240V	HP	25
		480V	HP	50
		600V	HP	40
for single-phase motor		120V	HP	5
		240V	HP	15
<b>Ambient conditions</b>				
Temperature				
Operating temperature		min	°C	-25
		max	°C	+55
Storage temperature		min	°C	-40
		max	°C	+70

**Resistance & Protection**


Frontal IP degree	IP40
Terminals IP degree	IP00

**Dimensions**



Series	Dimensions								L Number of elements											
	ØA	C	ØD	ØD2	E	H	ØK	ØN	1	2	3	4	5	6	7	8	9	10	11	12
7GN12	48	39.5	39	5	26.5	5	36	6	38.1	47.8	57.5	67.2	76.9	86.6	96.3	106	115.7	125.4	135.1	144.8
7GN20	48	39.5	39	5	26.5	5	36	6	38.1	47.8	57.5	67.2	76.9	86.6	96.3	106	115.7	125.4	135.1	144.8
7GN25	48	39.5	43	5	26.5	5	36	6	42.5	56.1	69.7	83.3	96.9	110.5	124.1	137.7	151.3	164.9	178.5	192.1
7GN32	65	53	58	5	34.5	5.5	48	7	48.5	63.6	78.7	93.8	108.9	124	139.1	154.2	169.3	184.4	199.5	214.6
7GN40	65	53	58	5	34.5	5.5	48	7	48.5	63.6	78.7	93.8	108.9	124	139.1	154.2	169.3	184.4	199.5	214.6
7GN63	65	53	62	6	34.5	7.5	68	7	53.3	71.4	89.5	107.6	125.7	143.8	161.9	180	198.1	216.2	234.3	252.4
7GN125	90	70.5	86	6	41.4	7.5	68	9	74.8	103.9	133	162.1	191.2	220.3	249.4	278.5	307.6	336.7	365.8	394.9

**Wiring diagrams**



**Certifications and compliance**

**Compliance**

- CSA C22.2 n° 14
- IEC/EN/BS 60947-1
- IEC/EN/BS 60947-3
- IEC/EN/BS 60947-5-1
- UL60947-4-1

**Certificates**

- EAC
- UL

**ETIM classification**

ETIM 8.0

EC001029 -  
Selector switch,  
complete