

| | | | |
|---|--|----|-----------|
| Product designation | Enclosed rotary cam switch | | |
| Product type designation | 7GN125 | | |
| General characteristics | | | |
| Switching diagram | 11 - 3-phase motor reversing switch | | |
| N° of elements | 3 | | |
| Mounting form | P25 - Plastic enclosure with red/yellow handle | | |
| Contact characteristics | | | |
| Rated insulation voltage U_i | IEC/EN | V | 690 |
| | UL/CSA | V | 600 |
| Rated impulse withstand voltage U_{imp} | | kV | 6 |
| Conventional free air thermal current I_{th} | IEC/EN | A | 125 |
| | UL/CSA | A | 130 |
| Rated operational voltage | | V | 690 |
| Rated operational impulse voltage | | kV | 6 |
| Maximum fuse size for short-circuit protection I_n (gG) | 10kA | A | 125 |
| | 15kA | A | 100 |
| | 25kA | A | 100 |
| | 50kA | A | 100 |
| | 63kA | A | 100 |
| Rated short time current I_{cw} | 1s | kA | 2100 |
| | | | 10/5 mA/V |
| Conductivity | 10/5 mA/V | | |
| Operational current I_e IEC/EN | AC1/AC21A | | |
| | | A | 125 |
| AC15 | 110V | A | 40 |
| | 220/230V | A | 28 |
| | 380/400V | A | 15 |
| | 660/690V | A | 5 |
| | Rated operational power in AC | | |
| Three-phase AC-3 | 220/230V | kW | 18.5 |
| | 380/440V | kW | 37 |
| | 500/690V | kW | 33 |
| Single-phase AC-3 | 110V | kW | 5 |
| | 220/230V | kW | 11 |
| | 380/440V | kW | 15 |
| Three-phase AC23A | 220/230V | kW | 30 |
| | 380/440V | kW | 45 |
| | 500/690V | kW | 37 |
| Single-phase AC23A | 110V | kW | 5 |
| | 220/230V | kW | 11 |


| | | 380/440V | kW | 15 |
|--|--|----------|-----------------|-------------------|
| Rated operational current in DC | | | | |
| DC21A | | 48V | A | 125 |
| | | 60V | A | 80 |
| | | 110V | A | 10 |
| | | 220V | A | 1.2 |
| DC23A (poles in series) | | 24V | A | 125 (1) |
| | | 48V | A | 125 (2) |
| | | 60V | A | 125 (3) |
| | | 110V | A | 50 (3) |
| | | 220V | A | 20 (4) |
| DC13 | | 24V | A | 125 |
| | | 48V | A | 100 |
| | | 60V | A | 50 |
| | | 110V | A | 4 |
| Power dissipation | | | W | 6.3 |
| Mechanical features | | | | |
| Terminals screw | | | | M2X5 |
| Tightening torque for terminals max | | | Nm | 2 |
| Conductor size | | | | |
| AWG - Rigid cable | | min | AWG | 14 |
| | | Max | AWG | 1/0 |
| AWG - Flexible cable | | min | AWG | 14 |
| | | Max | AWG | 1/0 |
| Conductor size (IEC) - Flexible cable | | min | mm ² | 2.5 |
| | | Max | mm ² | 50 |
| Conductor size (IEC) - Rigid cable | | min | mm ² | 2.5 |
| | | Max | mm ² | 50 |
| Mechanical life | | | cycles | 1X10 ⁶ |
| UL technical data | | | | |
| Motor power for direct-on-line control | | | | |
| for three-phase motor | | 120V | HP | 15 |
| | | 240V | HP | 25 |
| | | 480V | HP | 50 |
| | | 600V | HP | 40 |
| for single-phase motor | | 120V | HP | 5 |
| | | 240V | HP | 15 |
| Ambient conditions | | | | |
| Temperature | | | | |
| Operating temperature | | min | °C | -25 |
| | | max | °C | +55 |
| Storage temperature | | min | °C | -40 |
| | | max | °C | +70 |

Resistance & Protection

Frontal IP degree IP65


Terminals IP degree IP00

Dimensions



| Series | Enclosure size | Number of elements | | Dimensions | | | | | | | | | | Cable entry | Protection degree |
|--------|----------------|--------------------|-----|------------|-----|------|-----|-----|----|----|------|------|-------|------------------|-------------------|
| | | L | L1 | A | A1 | C | C1 | D | F | M | N | L | L1 | | |
| 7GN12 | 75x75 | 1-2 | 3-4 | 75 | 75 | 50 | 64 | 4.5 | 19 | 14 | 28 | 57.5 | 79.8 | 4xPG13.5 | IP65 |
| 7GN20 | | 1-2 | 3-4 | | | | | | | | | | | | |
| 7GN25 | | 1 | 2-3 | | | | | | | | | | | | |
| 7GN12 | 90x90 | 1-3 | 4-6 | 90 | 90 | 79 | 63 | 4.5 | 25 | 19 | 30 | 71.3 | 98.3 | 4xPG16 | IP65 |
| 7GN20 | | 1-3 | 4-6 | | | | | | | | | | | | |
| 7GN25 | | 1-2 | 3-4 | | | | | | | | | | | | |
| 7GN32 | | 1-2 | 3-4 | | | | | | | | | | | | |
| 7GN40 | | 1 | 2-3 | | | | | | | | | | | | |
| 7GN12 | 110x110 | 1-4 | 5-8 | 110 | 110 | 98.4 | 83 | 4.5 | 32 | 21 | 39.5 | 85.5 | 119.5 | 4xPG21 | IP65 |
| 7GN20 | | 1-4 | 5-8 | | | | | | | | | | | | |
| 7GN25 | | 1-3 | 4-5 | | | | | | | | | | | | |
| 7GN32 | | 1-3 | 4-5 | | | | | | | | | | | | |
| 7GN40 | | 1-2 | 3-5 | | | | | | | | | | | | |
| 7GN63 | | 1-2 | 3-4 | | | | | | | | | | | | |
| 7GN32 | 125x175 | 1-3 | 4-5 | 125 | 175 | 146 | 112 | 5.5 | 32 | 21 | 68 | 84.3 | 118.3 | 4xPG21 2xPG11 | IP65 |
| 7GN40 | | 1-2 | 3-4 | | | | | | | | | | | | |
| 7GN63 | | 1-2 | 3-4 | | | | | | | | | | | | |
| 7GN125 | | 1 | 2 | | | | | | | | | | | | |
| 7GN32 | 180x254 | 1-5 | 6-8 | 180 | 254 | 120 | 190 | 5.5 | 32 | 35 | 76 | 121 | 175 | 4xPG29 2xPG11 | IP65 |
| 7GN40 | | 1-4 | 5-7 | | | | | | | | | | | | |
| 7GN63 | | 1-3 | 4-6 | | | | | | | | | | | | |
| 7GN125 | | 1-2 | 3-4 | | | | | | | | | | | | |

Wiring diagrams



Certifications and compliance

Compliance

IEC/EN/BS 60947-1

IEC/EN/BS 60947-3

IEC/EN/BS 60947-5-1

Certificates

EAC

ETIM classification

ETIM 8.0

EC001029 -
Selector switch,
complete