

|   |                   |     |     |  |
|---|-------------------|-----|-----|--|
| Product designation                                       |                   |     |     | Rotary cam switches  |
| Product type designation                                  |                   |     |     | 7GN25  |
| <b>General characteristics</b>                            |                   |     |     |  |
| Switching diagram   |                   |     |     | 26 - 3-phase motor reversing switch with spring return                     |
| N° of elements  |                   |     |     | 3  |
| Mounting form   |                   |     |     | U47 - Snap on front mounting with black handle for hole diam. 22mm finxing |
| <b>Contact characteristics</b>                            |                   |     |     |  |
| Rated insulation voltage $U_i$                            | IEC/EN            | V   | 690 |  |
|   | UL/CSA            | V   | 600 |  |
| Rated impulse withstand voltage $U_{imp}$                 |                   |     | kV  | 6  |
| Conventional free air thermal current $I_{th}$            | IEC/EN            | A   | 25  |  |
|   | UL/CSA            | A   | 30  |  |
| Rated operational voltage                                 |                   |     | V   | 480  |
| Rated operational impulse voltage                         |                   |     | kV  | 4  |
| Maximum fuse size for short-circuit protection $I_n$ (gG) | 10kA              | A   | 25  |  |
|   | 15kA              | A   | 25  |  |
|   | 25kA              | A   | 25  |  |
| Rated short time current $I_{cw}$                         |                   |     | 1s  | kA   |
|   |                   |     |     | 400  |
| Conductivity  |                   |     |     | 10/5 mA/V  |
| Operational current $I_e$ IEC/EN                          | AC1/AC21A         |     | A   | 25   |
|   | AC15              |     |     |  |
|   | 110V              | A   | 16  |  |
|   | 220/230V          | A   | 12  |  |
|   | 380/400V          | A   | 8   |  |
|   | 660/690V          | A   | 2   |  |
| Rated operational power in AC                             | Three-phase AC-3  |     |     |  |
|   | 220/230V          | kW  | 5.5 |  |
|   | 380/440V          | kW  | 7.5 |  |
|   | 500/690V          | kW  | 7.5 |  |
|   | Single-phase AC-3 |     |     |  |
|   | 110V              | kW  | 1.5 |  |
|   | 220/230V          | kW  | 3   |  |
|   | 380/440V          | kW  | 5.5 |  |
|   | Three-phase AC23A |     |     |  |
|   | 220/230V          | kW  | 6.5 |  |
|   | 380/440V          | kW  | 11  |  |
|   | 500/690V          | kW  | 11  |  |
| Single-phase AC23A  |                   |     |     |  |
| 110V  | kW                | 1.5 |     |  |


|   |          |                 |                   |
|---|----------|-----------------|-------------------|
|   | 220/230V | kW              | 3.7               |
|   | 380/440V | kW              | 5.5               |
| <b>Rated operational current in DC</b>        |          |                 |                   |
| DC21A   |          |                 |                   |
|   | 48V      | A               | 25                |
|   | 60V      | A               | 25                |
|   | 110V     | A               | 4                 |
|   | 220V     | A               | 0.7               |
| <b>DC23A (poles in series)</b>                |          |                 |                   |
|   | 24V      | A               | 25 (1)            |
|   | 48V      | A               | 25 (2)            |
|   | 60V      | A               | 25 (3)            |
|   | 110V     | A               | 12 (3)            |
|   | 220V     | A               | 10 (4)            |
| <b>DC13</b>                                   |          |                 |                   |
|   | 24V      | A               | 25                |
|   | 48V      | A               | 20                |
|   | 60V      | A               | 16                |
|   | 110V     | A               | 1.5               |
|   | 220V     | A               | 0.4               |
| <b>Power dissipation</b>                      |          | W               | 1.1               |
| <b>Mechanical features</b>                    |          |                 |                   |
| <b>Terminals screw</b>                        |          |                 | M3.5              |
| <b>Tightening torque for terminals max</b>    |          | Nm              | 0.8               |
| <b>Conductor size</b>                         |          |                 |                   |
| AWG - Rigid cable                             |          |                 |                   |
|   | min      | AWG             | 20                |
|   | Max      | AWG             | 10                |
| AWG - Flexible cable                          |          |                 |                   |
|   | min      | AWG             | 20                |
|   | Max      | AWG             | 12                |
| Conductor size (IEC) - Flexible cable         |          |                 |                   |
|   | min      | mm <sup>2</sup> | 0.5               |
|   | Max      | mm <sup>2</sup> | 4                 |
| Conductor size (IEC) - Rigid cable            |          |                 |                   |
|   | min      | mm <sup>2</sup> | 0.5               |
|   | Max      | mm <sup>2</sup> | 4                 |
| <b>Mechanical life</b>                        |          | cycles          | 5x10 <sup>6</sup> |
| <b>UL technical data</b>                      |          |                 |                   |
| <b>Motor power for direct-on-line control</b> |          |                 |                   |
| for three-phase motor                         |          |                 |                   |
|   | 120V     | HP              | 3                 |
|   | 240V     | HP              | 5                 |
|   | 480V     | HP              | 10                |
|   | 600V     | HP              | 15                |
| for single-phase motor                        |          |                 |                   |
|   | 120V     | HP              | 1.5               |
|   | 240V     | HP              | 3                 |
| <b>Ambient conditions</b>                     |          |                 |                   |
| <b>Temperature</b>                            |          |                 |                   |
| Operating temperature                         |          |                 |                   |
|   | min      | °C              | -25               |
|   | max      | °C              | +55               |
| Storage temperature                           |          |                 |                   |

|     |    |     |
|-----|----|-----|
| min | °C | -40 |
| max | °C | +70 |

**Resistance & Protection**


|                     |      |
|---------------------|------|
| Frontal IP degree   | IP40 |
| Terminals IP degree | IP00 |

**Dimensions**



| Series | Dimensions |      | L    |      |       |       |
|--------|------------|------|------|------|-------|-------|
|        | □A         | E    | 1    | 2    | 3...8 | 8     |
| 7GN12  | 48         | 26.5 | 58   | 67.7 | 77.4  | 125.9 |
| 7GN20  | 48         | 26.5 | 58   | 67.7 | 77.4  | 125.9 |
| 7GN25  | 48         | 26.5 | 62.4 | 76   | 89.6  | 157.6 |

**Wiring diagrams**



**Certifications and compliance**

**Compliance**

- CSA C22.2 n° 14
- IEC/EN/BS 60947-1
- IEC/EN/BS 60947-3
- IEC/EN/BS 60947-5-1
- UL60947-4-1

**Certificates**

- cCSAus
- EAC
- UL

**ETIM classification**

ETIM 8.0

EC001029 -  
Selector switch,  
complete