

Product designation				Rotary cam switches	
Product type designation				7GN32	
General characteristics					
Switching diagram				13 - Dahlander motor control switch 1-0-2	
N° of elements				4	
Mounting form				O98 - Rear mounting with red/yellow handle padlockable in 0, door coupling and protection covers	
Contact characteristics					
Rated insulation voltage U_i	IEC/EN	V	690		
	UL/CSA	V	600		
Rated impulse withstand voltage U_{imp}			kV	6	
Conventional free air thermal current I_{th}	IEC/EN	A	32		
	UL/CSA	A	40		
Rated operational voltage			V	480	
Rated operational impulse voltage			kV	4	
Maximum fuse size for short-circuit protection I_n (gG)	10kA	A	32		
	15kA	A	32		
	25kA	A	32		
	50kA	A	32		
Rated short time current I_{cw}			1s	kA	
				800	
Conductivity				10/5 mA/V	
Operational current I_e IEC/EN	AC1/AC21A			A	
				32	
AC15	110V	A	25		
	220/230V	A	20		
	380/400V	A	10		
	660/690V	A	2		
Rated operational power in AC	Three-phase AC-3				
	220/230V	kW	7.5		
	380/440V	kW	11		
	500/690V	kW	11		
	Single-phase AC-3				
	110V	kW	2.2		
	220/230V	kW	4		
	380/440V	kW	6.5		
	Three-phase AC23A				
220/230V	kW	8			
380/440V	kW	15			
500/690V	kW	18.5			

Single-phase AC23A			
	110V	kW	2.2
	220/230V	kW	4
	380/440V	kW	7.5
Rated operational current in DC			
DC21A			
	48V	A	32
	60V	A	32
	110V	A	6
	220V	A	0.9
DC23A (poles in series)			
	24V	A	32 (1)
	48V	A	32 (2)
	60V	A	32 (3)
	110V	A	15 (3)
	220V	A	12 (4)
DC13			
	24V	A	32
	48V	A	25
	60V	A	16
	110V	A	3
	220V	A	0.5
Power dissipation		W	1.5
Mechanical features			
Terminals screw			M4
Tightening torque for terminals max		Nm	1.2
Conductor size			
AWG - Rigid cable			
	min	AWG	16
	Max	AWG	8
AWG - Flexible cable			
	min	AWG	16
	Max	AWG	10
Conductor size (IEC) - Flexible cable			
	min	mm ²	1.5
	Max	mm ²	4
Conductor size (IEC) - Rigid cable			
	min	mm ²	1.5
	Max	mm ²	6
Mechanical life		cycles	5x10 ⁶
UL technical data			
Motor power for direct-on-line control			
for three-phase motor			
	120V	HP	5
	240V	HP	10
	480V	HP	15
	600V	HP	15
for single-phase motor			
	120V	HP	2
	240V	HP	5
Ambient conditions			
Temperature			
Operating temperature			
	min	°C	-25

Storage temperature	max	°C	+55
	min	°C	-40
	max	°C	+70

Resistance & Protection

Frontal IP degree	IP40
Terminals IP degree	IP00

ETIM classification

ETIM 8.0	EC001029 - Selector switch, complete
----------	--