

Product designation	Enclosed rotary cam switch		
Product type designation	7GN63		
General characteristics			
Switching diagram	53 - Changeover switch 3 poles - 2 speed motor starting with separate windings		
N° of elements	3		
Mounting form	P25 - Plastic enclosure with red/yellow handle		
Contact characteristics			
Rated insulation voltage U_i	IEC/EN	V	690
	UL/CSA	V	600
Rated impulse withstand voltage U_{imp}		kV	6
Conventional free air thermal current I_{th}	IEC/EN	A	63
	UL/CSA	A	60
Rated operational voltage		V	480
Rated operational impulse voltage		kV	4
Maximum fuse size for short-circuit protection I_n (gG)	10kA	A	63
	15kA	A	63
	25kA	A	63
	50kA	A	63
	63kA	A	63
Rated short time current I_{cw}	1s	kA	1600
			10/5 mA/V
Conductivity	10/5 mA/V		
Operational current I_e IEC/EN	AC1/AC21A		
		A	63
AC15	110V	A	32
	220/230V	A	25
	380/400V	A	15
	660/690V	A	4
	Rated operational power in AC		
Three-phase AC-3	220/230V	kW	11
	380/440V	kW	18.5
	500/690V	kW	18.5
Single-phase AC-3	110V	kW	3.7
	220/230V	kW	6.5
	380/440V	kW	11.5
Three-phase AC23A	220/230V	kW	12.5
	380/440V	kW	30
	500/690V	kW	30

Single-phase AC23A

110V	kW	3.7
220/230V	kW	7.5
380/440V	kW	12.5

Rated operational current in DC

DC21A

48V	A	63
60V	A	50
110V	A	8
220V	A	1

DC23A (poles in series)

24V	A	50 (1)
48V	A	50 (2)
60V	A	50 (3)
110V	A	25 (3)
220V	A	15 (4)

DC13

24V	A	63
48V	A	40
60V	A	28
110V	A	3.3

Power dissipation

W	3.4
---	-----

Mechanical features

Terminals screw

M5

Tightening torque for terminals max

Nm 2

Conductor size

AWG - Rigid cable

min	AWG	14
Max	AWG	6

AWG - Flexible cable

min	AWG	14
Max	AWG	8

Conductor size (IEC) - Flexible cable

min	mm ²	2.5
Max	mm ²	10

Conductor size (IEC) - Rigid cable

min	mm ²	2.5
Max	mm ²	16

Mechanical life

cycles 5x10⁶

UL technical data

Motor power for direct-on-line control

for three-phase motor

120V	HP	7.5
240V	HP	15
480V	HP	25
600V	HP	25

for single-phase motor

120V	HP	3
240V	HP	10

Ambient conditions

Temperature

Operating temperature

min	°C	-25
max	°C	+55

Storage temperature

min	°C	-40
max	°C	+70

Resistance & Protection

Frontal IP degree IP65

Terminals IP degree IP00

ETIM classification

ETIM 8.0

EC001029 -
Selector switch,
complete