


| | | | | |
|---|-------------------|------|-----|---|
| Product designation | | | | Rotary cam switches |
| Product type designation | | | | 7GN40 |
| General characteristics | | | | |
| Switching diagram | | | | 123 - Multi-step 0-1-2 2 poles |
| N° of elements | | | | 2 |
| Mounting form | | | | O - Rear mounting with black handle |
| Contact characteristics | | | | |
| Rated insulation voltage U_i | IEC/EN | V | 690 | |
| | UL/CSA | V | 600 | |
| Rated impulse withstand voltage U_{imp} | | | kV | 6 |
| Conventional free air thermal current I_{th} | IEC/EN | A | 40 | |
| | UL/CSA | A | 50 | |
| Rated operational voltage | | | V | 480 |
| Rated operational impulse voltage | | | kV | 4 |
| Maximum fuse size for short-circuit protection I_n (gG) | 10kA | A | 40 | |
| | 15kA | A | 40 | |
| | 25kA | A | 40 | |
| | 50kA | A | 40 | |
| | 63kA | A | 40 | |
| Rated short time current I_{cw} | | | 1s | kA |
| | | | | 1000 |
| Conductivity | | | | 10/5 mA/V |
| Operational current I_e IEC/EN | AC1/AC21A | | | A |
| | AC15 | | | |
| Rated operational power in AC | Three-phase AC-3 | | | |
| | 220/230V | kW | 8 | |
| | 380/440V | kW | 15 | |
| | 500/690V | kW | 15 | |
| | Single-phase AC-3 | | | |
| 110V | kW | 3 | | |
| 220/230V | kW | 6.5 | | |
| 380/440V | kW | 8 | | |
| Three-phase AC23A | | | | |
| 220/230V | kW | 8 | | |
| 380/440V | kW | 18.5 | | |
| 500/690V | kW | 22 | | |
| Single-phase AC23A | | | | |
| 110V | kW | 3 | | |
| 220/230V | kW | 6 | | |

| | | 380/440V | kW | 11 |
|--|--|----------|-----------------|-------------------|
| Rated operational current in DC | | | | |
| DC21A | | 48V | A | 40 |
| | | 60V | A | 40 |
| | | 110V | A | 6 |
| | | 220V | A | 0.9 |
| DC23A (poles in series) | | 24V | A | 40 (1) |
| | | 48V | A | 40 (2) |
| | | 60V | A | 40 (3) |
| | | 110V | A | 20 (3) |
| | | 220V | A | 12 (4) |
| DC13 | | 24V | A | 40 |
| | | 48V | A | 32 |
| | | 60V | A | 16 |
| | | 110V | A | 3 |
| Power dissipation | | | W | 2.0 |
| Mechanical features | | | | |
| Terminals screw | | | | M4 |
| Tightening torque for terminals max | | | Nm | 1.2 |
| Conductor size | | | | |
| AWG - Rigid cable | | min | AWG | 16 |
| | | Max | AWG | 8 |
| AWG - Flexible cable | | min | AWG | 16 |
| | | Max | AWG | 10 |
| Conductor size (IEC) - Flexible cable | | min | mm ² | 1.5 |
| | | Max | mm ² | 6 |
| Conductor size (IEC) - Rigid cable | | min | mm ² | 1.5 |
| | | Max | mm ² | 10 |
| Mechanical life | | | cycles | 5x10 ⁶ |
| UL technical data | | | | |
| Motor power for direct-on-line control | | | | |
| for three-phase motor | | 120V | HP | 5 |
| | | 240V | HP | 10 |
| | | 480V | HP | 20 |
| | | 600V | HP | 20 |
| for single-phase motor | | 120V | HP | 2 |
| | | 240V | HP | 5 |
| Ambient conditions | | | | |
| Temperature | | | | |
| Operating temperature | | min | °C | -25 |
| | | max | °C | +55 |
| Storage temperature | | min | °C | -40 |
| | | max | °C | +70 |

Resistance & Protection


| | |
|---------------------|------|
| Frontal IP degree | IP40 |
| Terminals IP degree | IP00 |

Dimensions



| Series | Dimensions | | | | | | | | L Number of elements | | | | | | | | | | | |
|--------|------------|------|----|-----|------|-----|----|----|----------------------|-------|------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| | □A | C | ØD | ØD2 | E | H | □K | □N | 1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12 |
| 7GN12 | 48 | 39.5 | 39 | 5 | 26.5 | 5 | 36 | 6 | 38.1 | 47.8 | 57.5 | 67.2 | 76.9 | 86.6 | 96.3 | 106 | 115.7 | 125.4 | 135.1 | 144.8 |
| 7GN20 | 48 | 39.5 | 39 | 5 | 26.5 | 5 | 36 | 6 | 38.1 | 47.8 | 57.5 | 67.2 | 76.9 | 86.6 | 96.3 | 106 | 115.7 | 125.4 | 135.1 | 144.8 |
| 7GN25 | 48 | 39.5 | 43 | 5 | 26.5 | 5 | 36 | 6 | 42.5 | 56.1 | 69.7 | 83.3 | 96.9 | 110.5 | 124.1 | 137.7 | 151.3 | 164.9 | 178.5 | 192.1 |
| 7GN32 | 65 | 53 | 58 | 5 | 34.5 | 5.5 | 48 | 7 | 48.5 | 63.6 | 78.7 | 93.8 | 108.9 | 124 | 139.1 | 154.2 | 169.3 | 184.4 | 199.5 | 214.6 |
| 7GN40 | 65 | 53 | 58 | 5 | 34.5 | 5.5 | 48 | 7 | 48.5 | 63.6 | 78.7 | 93.8 | 108.9 | 124 | 139.1 | 154.2 | 169.3 | 184.4 | 199.5 | 214.6 |
| 7GN63 | 65 | 53 | 62 | 6 | 34.5 | 7.5 | 68 | 7 | 53.3 | 71.4 | 89.5 | 107.6 | 125.7 | 143.8 | 161.9 | 180 | 198.1 | 216.2 | 234.3 | 252.4 |
| 7GN125 | 90 | 70.5 | 86 | 6 | 41.4 | 7.5 | 68 | 9 | 74.8 | 103.9 | 133 | 162.1 | 191.2 | 220.3 | 249.4 | 278.5 | 307.6 | 336.7 | 365.8 | 394.9 |

Wiring diagrams



| | | | | | |
|---|---|---|---|---|---|
| 0 | | | | | |
| 1 | X | | X | | X |
| 2 | | X | | X | X |

107
123
135

Certifications and compliance

Compliance

- CSA C22.2 n° 14
- IEC/EN/BS 60947-1
- IEC/EN/BS 60947-3
- IEC/EN/BS 60947-5-1
- UL60947-4-1

Certificates

- cCSAus
- EAC
- UL

ETIM classification

ETIM 8.0

EC001029 -
Selector switch,
complete