


| | | | | |
|---|--------------------|----------|------|--|
| Product designation | | | | Rotary cam switches |
| Product type designation | | | | GF10 |
| General characteristics | | | | |
| Switching diagram | | | | 135 - Multi-step 0-1-2 3 poles |
| N° of elements | | | | 3 |
| Mounting form | | | | U47 - Snap on front mounting with black handle for hole diam. 22mm finxing |
| Contact characteristics | | | | |
| Rated insulation voltage U_i | IEC/EN | V | 480 | |
| | UL/CSA | V | 240 | |
| Rated impulse withstand voltage U_{imp} | | | kV | 4 |
| Conventional free air thermal current I_{th} | IEC/EN | A | 10 | |
| | UL/CSA | A | 10 | |
| Rated operational voltage | | | V | 480 |
| Rated operational impulse voltage | | | kV | 4 |
| Maximum fuse size for short-circuit protection I_n (gG) | 10kA | A | 16 | |
| | | 1s | kA | 250 |
| Conductivity | | | | 10/5 mA/V |
| Operational current I_e IEC/EN | AC1/AC21A | | A | 10 |
| | AC15 | | | |
| | | 110V | A | 5 |
| | | 220/230V | A | 3 |
| | 380/400V | A | 2 | |
| Rated operational power in AC | Three-phase AC-3 | | | |
| | | 220/230V | kW | 1.5 |
| | | 380/440V | kW | 2.2 |
| | Single-phase AC-3 | | | |
| | | 110V | kW | 0.3 |
| | | 220/230V | kW | 0.55 |
| | | 380/440V | kW | 0.75 |
| | Three-phase AC23A | | | |
| | | 220/230V | kW | 1.8 |
| | | 380/440V | kW | 3 |
| | Single-phase AC23A | | | |
| | | 110V | kW | 0.7 |
| | 220/230V | kW | 0.75 | |
| | 380/440V | kW | 1.1 | |
| Rated operational current in DC | DC21A | | | |
| | | 48V | A | 10 |
| | | 60V | A | 7 |
| | | 110V | A | 2 |

| | | | | |
|--|---------------------------------------|------|-----------------|-------------------|
| | | 220V | A | 0.7 |
| | | 440V | A | 0.2 |
| DC13 | | 24V | A | 3 |
| | | 48V | A | 3 |
| | | 60V | A | 2 |
| | | 110V | A | 1 |
| | | 220V | A | 0.3 |
| | | 440V | A | 0.1 |
| Power dissipation | | | W | 0.4 |
| Mechanical features | | | | |
| Terminals screw | | | | 2.5M |
| Tightening torque for terminals max | | | Nm | 0.4 |
| Conductor size | | | | |
| | AWG - Rigid cable | | | |
| | | min | AWG | 20 |
| | | Max | AWG | 14 |
| | AWG - Flexible cable | | | |
| | | min | AWG | 20 |
| | | Max | AWG | 14 |
| | Conductor size (IEC) - Flexible cable | | | |
| | | min | mm ² | 0.5 |
| | | Max | mm ² | 1.5 |
| | Conductor size (IEC) - Rigid cable | | | |
| | | min | mm ² | 0.5 |
| | | Max | mm ² | 1.5 |
| Mechanical life | | | cycles | 1x10 ⁶ |
| UL technical data | | | | |
| Motor power for direct-on-line control | | | | |
| | for three-phase motor | | | |
| | | 240V | HP | 2 |
| | for single-phase motor | | | |
| | | 240V | HP | 0.75 |
| Ambient conditions | | | | |
| Temperature | | | | |
| | Operating temperature | | | |
| | | min | °C | -25 |
| | | max | °C | +55 |
| | Storage temperature | | | |
| | | min | °C | -40 |
| | | max | °C | +70 |
| Resistance & Protection | | | | |
| Frontal IP degree | | | | IP40 |
| Terminals IP degree | | | | IP20 |
| Dimensions | | | | |



| Series | Dimensions | | L | | | |
|--------|------------|------|----|------|-------|-------|
| | □A | E | 1 | 2 | 3...8 | |
| GF10 | 30 | 18.5 | 60 | 72 | 84 | 144 |
| GF20 | 48 | 26.5 | 56 | 69.5 | 83 | 150.5 |

Wiring diagrams



Certifications and compliance

Compliance

CSA C22.2 n° 14
IEC/EN/BS 60947-1
IEC/EN/BS 60947-3
IEC/EN/BS 60947-5-1
UL60947-4-1

Certificates

cULus
EAC

ETIM classification

ETIM 8.0

EC001029 -
Selector switch,
complete