



Coloane  
luminoase Ø50  
mm  
LTN50

Denumirea produsului

Denumirea tipului de produs

### Caracteristici generale

Diametru	mm - inch	50 / 1.97
Culoare		Verde
grad de protectie IEC		IP65
Consumul de energie	VA	1.2

### Caracteristici mecanice

Greutate	g	37
----------	---	----


### Conditii ambientale

Temperatura

Temperatura de Operare

min	°C	-30
max	°C	+50

### Dimensiuni



### Certificari si conformitate

Conformitate

CSA C22.2 n° 14  
IEC/EN/BS 60947-1  
IEC/EN/BS 60947-5-1  
UL508

Certificate

cULus

### Clasificare ETIM

ETIM 8.0

EC000232 -  
Modul optic  
pentru turn de  
semnalizare