



Product designation				Switch disconnecter
Product type designation				GA
Number of poles		Nr.		3
Operating voltage type				AC
Contact characteristics				
IEC Conventional free air thermal current I _{th}		A		160
Rated insulation voltage U _i IEC/EN		V		1000
Rated impulse withstand voltage U _{imp}		kV		8
Operating current I _e				
	AC21A			
		400V	A	160
		500V	A	160
		690V	A	160
	AC22A			
		400V	A	160
		500V	A	125
		690V	A	125
	AC23A			
		400V	A	125
		500V	A	100
		690V	A	47
Power dissipation per pole max			W	12
Rated operational power AC23A				
		400V	kW	55
		690V	kW	45
Rated short time current (1s) I _{cw} (rms)			kA	2.5
Conditional short-circuit current (rms)			kA	50
Short-circuit protection with fuse		Class/A		gG160
Making capacity AC23A 400V		A		1250
Breaking capacity AC23A 400V		A		1000
Mechanical life			cycles	30000
Electrical life AC21A			cycles	1500 (AC23A 400V)
Mechanical features				
Operating position		normal allowable		Vertical plan Any
Fixing				Screw / DIN rail 35mm
Terminals				
		type		Pillar
		width	mm	12.4
		height	mm	10.4
		screw		M8
		tool		Metric Allen key 4

Tightening torque for terminals

min	Nm	5
max	Nm	6
min	lbin	45
max	lbin	54

Conductor section

IEC min	mm ²	4
IEC max	mm ²	70
AWG/kcmil min		12
AWG/kcmil max		1

UL technical data

UL Standard	UL98
-------------	------

Minimum enclosure dimensions at rated current

mm	mm	150x140x110
in	in	5.9 x 5.5 x 4.3

Ambient conditions

Operating temperature

min	°C	-25
max	°C	+55

Storage temperature

min	°C	-40
max	°C	+70

Max altitude


m	3000
---	------

Resistance & Protection


Frontal IP degree	IP20
-------------------	------

Pollution degree	3
------------------	---

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

IEC/EN 60947-1

IEC/EN 60947-3

Certifications

CCC

EAC

ETIM classification

ETIM 8.0

EC000216 -
 Switch
 disconnecter