



Signal tower
Ø50mm/1.97"
LTN50

Product designation

Product type designation

General characteristics

Diameter	mm - inch	50 / 1.97
IEC degree of protection		IP20
Power consumption	VA	1.7
Sound intensity	dB	100

Mechanical features

Weight	g	48
--------	---	----


Ambient conditions

Temperature

Operating temperature

min	°C	-30
max	°C	+50

Dimensions



Certifications and compliance

Compliance

- CSA C22.2 n° 14
- IEC/EN/BS 60947-1
- IEC/EN/BS 60947-5-1
- UL508

Certificates

cULus

ETIM classification

ETIM 8.0

EC001261 -
Acoustic module
for signal tower