



Product designation
Product type designation
Motor type

Soft Starter
ADX
Asynchronous
three phase

Electrical features

Supplies voltage

Type of system	Three phase
Rated supply voltage	V 208...415VAC
auxiliary supply voltage (Us)	208...240VAC
Rated frequency	Hz 50/60

Rated starter current Ie	A	470
--------------------------	---	-----

Rated motor power

IEC ratings (T≤40°C)

230VAC	kW	132
400VAC	kW	250
500VAC	KW	315

UL ratings (T≤40°C)

220-240VAC	HP	150
380-415VAC	HP	250
440-480VAC	HP	350

Number of controlled phases	Nr.	3
-----------------------------	-----	---

Built-in bypass

No, predisposed
for external
bypass contactor

Cooling System

Forced

Programming interface

Display

Backlit LCD 2x16
character

Programming with NFC technology

No

Optical port

No

Startup and stop settings

Startup method

Torque or voltage
ramp with current
limitation

Stop method

Torque ramp,
voltage ramp,
free-wheel stop

Braking method

DC dynamic with
external relay

Protections

Auxiliary supply protection

Voltage too low

Power supply Protection	No power, phase loss, phase sequence, frequency out of limits, minimum and maximum voltage
Motor protection	Overload at starting (trip class 2, 10A, 10, 15, 20, 25, 30, 35 and 40), overload during running (trip class 2, 10A, 10, 15, 20, 25 and 30), locked rotor, current asymmetry, minimum torque (dry run), overtemperature, starting too long
Starter protection	Overcurrent, overtemperature, bypass failure, phase shorted, temperature sensor fault, maintenance request

Functions	
Built-in bypass	3
Built-in display and keypad	No
Languages	Yes
View measurements	4
Torque control	Yes
Adjustable current limit	Yes
Dynamic braking	Yes
Kick Start function	Yes
Motor overload electronic protection	Yes
Motor protection PTC input	Yes
Protection against phase loss	Yes
Protection against phase inversion	Yes
Protection against locked rotor	Yes
Protection against thyristor overtemperature	Yes
Protection against low load	Yes
Programmable alarm	Yes
Digital inputs	Yes
Analog inputs	Yes
Digital outputs	Yes
Analog output	Yes
Monitoring communication	Yes
Optical port for programming	RS323
Event log	No
Motor hour counter	Yes

Startup counter		Yes
Clock calendar		Yes
Remote external keypad		Yes
Plug-in version		Optional
Input and Output		
Digital inputs		
	Number of digital input	Nr.
	Digital input type	
	Digital input functions	
Analog inputs		
	Number of analog input	Nr.
	Analog input type	


3 (2 digital inputs + 1 digital/analog input)
24VDC (no need for external feeder)
1 input for start, 1 input programmable (stop, free-wheel stopping, external alarm, motor preheat, local control, alarms inhibit, manual resetting of motor thermal protection, keypad lock, second motor), 1 input programmable multifunction (OFF, free-wheel stopping, external alarm, motor preheat, local control, alarms inhibit, manual resetting of motor thermal protection, keypad lock, second motor, cascade starting, 0-10V ramp, 2-10V ramp, 0-10V start-stop, PT100 start-stop, PTC protection)

1 (digital/analog)
0-10VDC (0-20mA with external resistor 500Ω)

		Motor protection via PTC probes, acceleration and/or deceleration ramp via analog input, analog input thresholds for motor starting and stopping, analog input thresholds for programmable relay enable and disable, PT100 input thresholds for motor starting and stopping and PT100 input thresholds for programmable relay enable and disable	
Analog input functions			
Digital outputs			
	Number of digital output	Nr.	4
	Digital output arrangement		3 x 1 NO (SPST) + 1 C/O (SPDT) Ratings: 5A 250VAC AC1, 2A 250VAC AC15 C/O output for global alarm, 3 x 1NO outputs programmable (OFF, motor powered, up to speed, braking, current limit, service required, cascade starting, programmable input thresholds, alarm Axx)
	Digital output functions		
Analog outputs			
	Number of analog output	Nr.	1
	Analog output type		0...20mA, 4...20mA (0...10V with external resistor 500Ω) Current, torque, motor thermal status, power factor and active power
	Analog output functions		
Ambient conditions			
Temperature			
	Operating temperature		
		min	°C -10

	max	°C	+55°C (with current derating >45°C of 1.5%/ °C)
Storage temperature	min max	°C °C	-30 +70
Max altitude		m	1000 without derating (over 1000mt with current derating of 0.5%/100m)
Relative humidity		%	95% without condensation or dripping
Pollution degree			3
Housing			
Mounting			Screw-fixing
IP degree of protection			IP00
Dimensions (W x H x D)	mm		790 x 650 x 430
Weight	Kg		95

Dimensions



TYPE	A	B	C	D	E	F
ADX 0310	640 (25.20")	600 (23.62")	380 (14.96")	620 (24.41")	400 (15.75")	100 (3.94")
ADX 0365	640 (25.20")	600 (23.62")	380 (14.96")	620 (24.41")	400 (15.75")	100 (3.94")
ADX 0470	790 (31.10")	650 (25.59")	430 (16.93")	770 (30.31")	450 (17.72")	100 (3.94")
ADX 0568	790 (31.10")	650 (25.59")	430 (16.93")	770 (30.31")	450 (17.72")	100 (3.94")
ADX 0640	790 (31.10")	650 (25.59")	430 (16.93")	770 (30.31")	450 (17.72")	100 (3.94")
ADX 0820	910 (35.83")	950 (37.40")	442 (17.40")	830 (32.68")	920 (36.22")	❶
ADX 1200	910 (35.83")	950 (37.40")	442 (17.40")	830 (32.68")	920 (36.22")	❶

❶ Consult Customer Service; see contact details on inside front cover.

Certifications and compliance

Compliance

IEC/EN 60947-1
IEC/EN 60947-4-2

Certificates

EAC

ETIM classification

ETIM 8.0

EC000640 - Soft
starter