



Product designation	Switch disconnecter		
Product type designation	GE		
Number of poles	Nr.	4	
Operating voltage type		AC	
Contact characteristics			
IEC Conventional free air thermal current I _{th}	A	800	
Rated insulation voltage U _i IEC/EN	V	1000	
Rated impulse withstand voltage U _{imp}	kV	12	
Operating current I _e			
AC21A			
	400V	A	800
	500V	A	800
	690V	A	800
AC22A			
	400V	A	800
	500V	A	800
	690V	A	500
AC23A			
	400V	A	800
	500V	A	500
	690V	A	315
Power dissipation per pole max	W	56	
Rated operational power AC23A			
	400V	kW	443
	690V	kW	300
Rated short time current (1s) I _{cw} (rms)	kA	16	
Conditional short-circuit current (rms)	kA	100	
Short-circuit protection with fuse	Class/A	gG800	
Making capacity AC23A 400V	A	6300	
Breaking capacity AC23A 400V	A	5000	
Mechanical life	cycles	10000	
Electrical life AC21A	cycles	500 (AC23A 400V)	
Mechanical features			
Operating position	normal allowable	Vertical plan Any	
Fixing		Screw	
Terminals	type screw	Bar M10	
Tightening torque for terminals	max	I _{bin}	10
Bar dimensions max		30x5	

Ambient conditions

Operating temperature

min	°C	-25
max	°C	55

Storage temperature

min	°C	-40
max	°C	70

Max altitude

m	3000
---	------

Resistance & Protection


Frontal IP degree

IP20

Pollution degree


3

Dimensions




Type	A	B	C
GE0500 T4	190 (7.48")	220 (8.66")	25 (0.98")
GE0630 DT4	205 (8.07")	235 (9.25")	30 (1.18")
GE0630 T4	205 (8.07")	235 (9.25")	30 (1.18")
GE0800 DT4	205 (8.07")	235 (9.25")	30 (1.18")
GE0800 T4	205 (8.07")	235 (9.25")	30 (1.18")


Direct operating version with handle GEX67ND



Door coupling version with handle GEX67N - GEX67NB




Drilling



Wiring diagrams

Four-pole disconnectors
GE0160 T4 - GE1600 T4
GE0160 T4P



Certifications and compliance

Compliance

IEC/EN 60947-1

IEC/EN 60947-3

Certifications

EAC

ETIM classification

ETIM 8.0

EC000216 -
 Switch
 disconnector