



Product designation	Switching power supplies		
Product type designation	PSL1		
Input characteristics			
Input type	Single-phase		
Rated supply voltage AC	VAC	Multivoltage 100...240	
Operating range	AC	min VAC	90
		Max VAC	264
	DC	min VDC	90
		Max VDC	375
Rated frequency		Hz	50/60
Operational frequency		min Hz	47
		max Hz	63
Current consumption Max		mA	1500
Insulation voltage Input/Output	AC	VAC	3000
	DC	VAC	4242
Internal fuse (250VAC)			T2A
Output characteristics			
Rated output voltage DC		VDC	48
Voltage trimming (potentiometer) DC		min VDC	48
		Max VDC	55
Rated output current		A	1.25
Rated output power		W	60
Temperature coefficient		%/°C	0.03
Line adjustment		%	±0.5
Load adjustment		%	±0.5
Efficiency		%	89
Overload protection			110...150%
Short-circuit protection			Fold forward
Ripple & noise		mV	50
Indications			
LED indicator for power on			Yes
Power Rdy (Ready - minimum limit)			Yes (transistor output - 18.8VDC)
Connections			
Terminals type			Screw
Ambient conditions			

Temperature

Operating temperature

min	°C	-40
max	°C	+71

Storage temperature

min	°C	-40
max	°C	+85

Derating

%/°C	2.5
------	-----

Housing

Material

Plastic

IEC degree of protection

IP20

Dimensions (W x H x D)

mm 40.5 x 90 x 115

Weight


g 400

Installations

Mounting


On 35mm DIN rail

Dimensions



TYPE	A	B	C
PSL1 005 24	22.5 (0.88")	90 (3.54")	115 (4.53")
PSL1 010 24	22.5 (0.88")	90 (3.54")	115 (4.53")
PSL1 018 24	22.5 (0.88")	90 (3.54")	115 (4.53")
PSL1 030...	40.5 (1.59")	90 (3.54")	115 (4.53")
PSL1 060...	40.5 (1.59")	90 (3.54")	115 (4.53")
PSL1 100...	54 (2.12")	90 (3.54")	115 (4.53")
PSL2 100...	54 (2.12")	90 (3.54")	115 (4.53")
PSLR 20 24	54 (2.12")	90 (3.54")	115 (4.53")

Wiring diagrams



Certifications and compliance

Compliance

CSA C22.2 n°14

IEC/EN/BS 61000-6-2

IEC/EN/BS 61000-6-3

IEC/EN/BS 62368-1

UL 508

Certificates

cULus

EAC

RCM

ETIM classification

ETIM 8.0

EC002540 - DC-
power supply