




Product designation			Switch disconnecter	
Product type designation			GL	
Number of poles			Nr.	4
Operating voltage type			AC	
Contact characteristics				
IEC Conventional free air thermal current I _{th}			A	1000
Rated insulation voltage U _i IEC/EN			V	1000
Rated impulse withstand voltage U _{imp}			kV	12
Operating current I _e				
AC21A				
			400V	A 1000
			500V	A 1000
			690V	A 1000
			1000V	A 1000
AC22A				
			400V	A 1000
			500V	A 1000
			690V	A 1000
AC23A				
			400V	A 1000
			500V	A 1000
			690V	A 1000
Power dissipation per pole max			W	63
Rated operational power AC23A				
			400V	kW 560
			690V	kW 1000
Rated short time current (1s) I _{cs} (rms)			kA	50
Conditional short-circuit current (rms)			kA	100
Short-circuit protection with fuse			Class/A	gG/1000
Making capacity AC23A 400V			A	10000
Breaking capacity AC23A 400V			A	8000
Mechanical life			cycles	3000
Mechanical features				
Operating position				
			normal allowable	Vertical plan Any
Fixing			Screw	
Terminals				
			type	M12
Tightening torque for terminals				
			min	Nm 50
			max	Nm 75
			min	lbin 442
			max	lbin 664

Ambient conditions

Operating temperature	min	°C	-25
	max	°C	+55
Storage temperature	min	°C	-40
	max	°C	+70
Max altitude		m	3000

Wiring diagrams



Certifications and compliance

Compliance	IEC/EN/BS 60947-1
	IEC/EN/BS 60947-3

ETIM classification

ETIM 8.0	EC000216 - Switch disconnect
----------	------------------------------------