



Product designation	Switching power supplies		
Product type designation	PSL3		
Input characteristics			
Input type	Three-phase		
Rated supply voltage AC	VAC	Multivoltage 400...500	
Operating range			
AC	min	VAC	340
	Max	VAC	575
DC	min	VDC	480
	Max	VDC	820
Rated frequency		Hz	50/60
Operational frequency	min	Hz	47
	max	Hz	63
Current consumption Max		mA	850
PFC			0.55
Insulation voltage Input/Output	AC	VAC	3000
	DC	VAC	4242
Internal fuse (250VAC)			T2A
Output characteristics			
Rated output voltage DC		VDC	48
Voltage trimming (potentiometer) DC	min	VDC	47
	Max	VDC	56
Rated output current		A	5
Rated output power		W	240
Temperature coefficient		%/°C	0.03
Line adjustment		%	±1
Load adjustment		%	±1
Efficiency		%	91
Overload protection			120...140%
Short-circuit protection			Hiccup
Ripple & noise		mV	100
Parallel connection		Nr.	2
Indications			
LED indicator for power on			Yes
LED indicator for low voltage			Yes
Power Rdy (Ready - minimum limit)			Yes (transistor output - 60VDC)
Connections			

Terminals type Screw

Ambient conditions

Temperature

Operating temperature	min	°C	-40
	max	°C	+71

Storage temperature	min	°C	-40
	max	°C	+85

Derating %/°C 2.5

Housing

Material Metal

IEC degree of protection IP20


Dimensions (W x H x D) mm 89 x 124 x 118.8

Weight g 1190

Installations


Mounting On 35mm DIN rail

Dimensions



TYPE	A	B	C
PSL1 120...	64 (2.52")	124.5 (4.90")	123.6 (4.87")
PSL1 240...	83.5 (3.29")	124.5 (4.90")	123.6 (4.87")
PSL1 300...	83.5 (3.29")	124.5 (4.90")	123.6 (4.87")
PSL1 480...	175.5 (6.91")	124.5 (4.90")	123.6 (4.87")
PSL3 120 24	74.3 (2.92")	124 (4.88")	118.8 (4.68")
PSL3 240...	89 (3.50")	124 (4.88")	118.8 (4.68")
PSL3 480...	150 (5.90")	124 (4.88")	118.8 (4.68")
PSL3 960...	275.8 (10.86")	125.9 (4.96")	120.3 (4.74")

Wiring diagrams



Certifications and compliance

Compliance

- CSA C22.2 n°14
- IEC/EN/BS 61000-6-2
- IEC/EN/BS 61000-6-3
- IEC/EN/BS 62368-1
- UL 508

Certificates

- cULus
- EAC
- RCM

ETIM classification

ETIM 8.0

EC002540 - DC-
power supply